










## Notes:

- 1.Current Rating: 24V&5A max.
- 2.Contact Resistance: 50mOhms Max.(initial)
- 3.Insulation Resistance: 100M Ohms Min./500V DC
- 4.Dielectric Withstanding Voltage: 500V AC/1Minute
- 5.Mating Force: 35N Max, Withdrawal Force: 3N Min.
- 6.Durability: 5,000 Cycles
- 7.Operating Temperature:-25°C to+85°C

|      |             |     |                                                                                                           |
|------|-------------|-----|-----------------------------------------------------------------------------------------------------------|
| 7    | BOND        | 1   | EPOXY, BLACK                                                                                              |
| 6    | BACK COVER  | 1   | HIGH TEMPERATURE, BLACK                                                                                   |
| 5    | HOUSING     | 1   | HIGH TEMPERATURE, BLACK                                                                                   |
| 4    | TERMINAL 4# | 1   | STAINLESS STEEL; NICKEL PLATING                                                                           |
| 3    | TERMINAL 3# | 1   | COPPER ALLOY; NICKEL UNDER PLATING OVERALL, Sn PLATING ON SOLDER AREA, GOLD FLASH PLATING ON CONTACT AREA |
| 2    | TERMINAL 2# | 1   | COPPER ALLOY; NICKEL UNDER PLATING OVERALL, Sn PLATING ON SOLDER AREA, GOLD FLASH PLATING ON CONTACT AREA |
| 1    | CENTER PIN  | 1   | COPPER ALLOY; NICKEL UNDER PLATING OVERALL, Sn PLATING ON SOLDER AREA, Ni FLASH PLATING ON CONTACT AREA   |
| ITEM | NAME        | QTY | DESCRIPTION                                                                                               |



深圳市华宇创精密电子有限公司

|                                                                           |                    |                      |                              |
|---------------------------------------------------------------------------|--------------------|----------------------|------------------------------|
| TOLERANCE:<br>X.X ±0.30<br>X.XX ±0.25<br>X.XXX ±0.15<br>X' ±2" X.X" ±0.5" | DRAWN BY :<br>陈一鸣  | DATE :<br>2014-02-23 | PART NAME:<br>防水DC           |
| UNIT: mm [inch]                                                           | CHECKED BY:<br>马跃  | DATE :<br>2014-02-23 | PART NO.<br>HYCW-DC1852-250B |
| SCALE:1:1 SIZE: A4                                                        | APPROVED BY:<br>邱敏 | DATE :<br>2014-02-23 | MOLD NO.                     |
|                                                                           |                    |                      | DRAW NO:<br>HYC-2205201606   |
|                                                                           |                    |                      | SHEET NO.<br>1 OF 1          |

