


LTR	DESCRIPTION	DATE	APPROVED
B	RELEASED PER ECO-15-005340	04/07/2015	I. MYONG



MATERIAL:

- BASE METAL – ALLOY C17200 OR C17300 PER ASTM B196/B196M
 PLATINGS – ELECTROLESS NICKEL CONFORMING TO SAE AMS-C-26074, CLASS 3, GRADE C
 – CADMIUM OLIVE DRAB CONFORMING TO SAE AMS-QQ-P-416 TYPE II CLASS 3 (500 HOUR SALT SPRAY)
 – TIN/NICKEL PER TYCO ES-61400/32

APPLICATION:

1. THESE DEVICES ARE DESIGNED TO BE USED IN A HEXASHIELDF EMI TERMINATION SYSTEM.


PART NUMBERING:

FLX40-03X-XX

- 01: PASS-THROUGH, SIZE 06
- 02: PLUG, SIZE 06
- 0: ELECTROLESS NICKEL
- 1: CADMIUM OLIVE DRAB
- 2: TIN/NICKEL

©2015 TE CONNECTIVITY LTD. FAMILY OF COMPANIES. ALL RIGHTS RESERVED.
 TE CONNECTIVITY (LOGO) AND TE (LOGO) ARE TRADEMARKS.
 OTHER LOGOS, PRODUCT AND/OR COMPANY NAMES MAY BE TRADEMARKS OF THEIR RESPECTIVE OWNERS.

Raychem Adapters
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. METRIC DIMENSIONS ARE IN BRACKETS.	DRAWN N. SWATKO	DATE 04/01/2015	TE CONNECTIVITY			
	CHECKED I. MYONG	DATE 04/01/2015				
TYCO ELECTRONICS RESERVES THE RIGHT TO CHANGE THIS DRAWING AT ANYTIME USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.	APPROVED I. MYONG	DATE 04/01/2015	TITLE FERRULE, PASS-THROUGH AND PLUG HEXASHIELDF EMI TERMINATION SYSTEM			
	CAD FILE NAME: FLX40-03X-XX.dwg					
DECIMAL TOLERANCES: .XXX ±.005 [0,13mm] .XX ±.01 [0,25mm] .X ±.1 [2,54mm]	THIRD ANGLE PROJECTION: 		SIZE A	CAGE 06090	DWG. NO. FLX40-03X-XX	REV B
ANGULAR TOLERANCE: .X ±1°			DO NOT SCALE THIS DRAWING			
			SHEET 1 OF 1			