





| 版次<br>REV | 更改单号<br>Revise No | 制图绘图<br>DESCRIPTION | 日期<br>Date |
|-----------|-------------------|---------------------|------------|
| A         |                   |                     |            |
| B         |                   |                     |            |
| C         |                   |                     |            |



PCB线路板安装图(±0.1)

- 技术参数:
1. 做用温度: -20 ~+70 .
  2. 额定负荷: DC 12V 50mA;
  3. 接触电阻: ≤50mΩ;
  4. 绝缘电阻: ≥100MΩ;
  5. 耐 压: AC250V(50Hz)/min;
  6. 动 作 力: 250±50g;
  7. 使用寿命: 50000次;
  8. 未注尺寸公差参照下面表格.

|                           |  |                 |  |                      |  |                     |  |
|---------------------------|--|-----------------|--|----------------------|--|---------------------|--|
| 首韩®<br>SHOUHAN            |  | 深圳市首韩科技有限公司     |  | 名 称<br>Denomination: |  | 轻触开关<br>TACT SWITCH |  |
| 未注公差<br>General tolerance |  | 设计<br>Design:   |  | 型 号<br>Part no.:     |  | TS4555B3J           |  |
| .X ±0.20 .X' ±1'          |  | 校对<br>Check:    |  | 单位<br>Unit: mm       |  | 图 幅<br>DIN          |  |
| .X ±0.15 .X' ±0.5'        |  | 审核<br>Auditing: |  | 阶段标记<br>Phase marker |  | 重量<br>Weight        |  |
| .XX ±0.05 .XX' ±0.1'      |  | 批准<br>Approve:  |  | 比例<br>Scale          |  | 页 码<br>Sheet of     |  |
| .XXX ± .XXX' ±            |  | 罗孝金             |  |                      |  | 版 次<br>REV          |  |
|                           |  |                 |  |                      |  | A/0                 |  |



深圳市首韩科技有限公司

SHENZHEN SHOUHAN TECHNOLOGY CO., LTD

Tel: 0755-27597601 Fax: 0755-27597491

## 承 认 书

### SPECIFICATION FOR APPROVAL

产 品 编 码  
Material code:

产品名称 Project: 轻触开关

规格型号 Part No: TS4555B3J

贵公司承认印 Approval signatures

| 料 号/Part No. | 签 章/Signatures |
|--------------|----------------|
|              |                |

日期 Date:

|             |     |                                                                                      |
|-------------|-----|--------------------------------------------------------------------------------------|
| 拟制/Drawn    | 李春风 |  |
| 审核/Check    | 钟华华 |                                                                                      |
| 批准/Approved | 罗孝金 |                                                                                      |



# 产 品 规 格 书

## PRODUCT SPECIFICATION

|                               |                                    |                                                                                                                                                                      |                                                                                     |
|-------------------------------|------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| SIRLES                        |                                    | 系列:FLIP SWITCHES(轻触开关)                                                                                                                                               |                                                                                     |
| MODEL                         |                                    | 型号: TS4555B3J                                                                                                                                                        |                                                                                     |
| 1.RATING                      |                                    | 额定值:50mA 12V DC                                                                                                                                                      |                                                                                     |
| 2.CONSTRUTION DIMENSION 结构尺寸  |                                    | Apply to the appended drawing:符合附加图纸                                                                                                                                 |                                                                                     |
| 3.APEARANCE 外观                |                                    | Have no remarkable damage,crack and rust etc:无明显损伤,裂纹,锈迹等.                                                                                                           |                                                                                     |
| 4.CONTACTLOOP 接触回路            |                                    | Monople loop:单通单极回路                                                                                                                                                  |                                                                                     |
| ITEM 专案                       |                                    | TEST CONDITION 测试条件                                                                                                                                                  | SPECIFICATION 规格                                                                    |
| 5.CAPABILITY OF ELECTRIC 电气性能 |                                    |                                                                                                                                                                      |                                                                                     |
| 5A                            | INSULATION RESISTANCE<br>绝缘电阻      | Measurements shall be made following Application of DC100V potential across terminals and across terminals and fuame for 1minute,在端子之间和端子与壳之间加 DC100V 条件下,持续 1 分钟测量. | 100M $\Omega$ min<br>100 M $\Omega$ 以上.                                             |
| 5B                            | WITHSTAND VILTAGE<br>耐电压           | AC250V、50HZ、1 min (imin(interrupting current $\leq$ 500uA). AC250V、50HZ、1 分钟(漏电流 500uA)                                                                              | There shall be no briakdown 无击穿现象出现。                                                |
| 5C                            | CONTACT CIRCUIT<br>接触电路            | Addition 1.5-2 time force on the top of the keystrok and press the switch,DC50V100mA 在按键顶端上等于作用力 1.5-2 倍的力按动开关,DC50V,10Ma.                                           | 50m $\Omega$ Max<br>(50m $\Omega$ 以下).                                              |
| 5D                            | SWITCH CONNECTION FLASH<br>开关接触点抖动 | Addition DC5V on the two side of switch,at a speed of 3-5time a sec.to press the switch.在开关的两端加 DC5V 的电压,以 3-5 次/秒的速度按动开关.                                           | The flash time between open not more than 10ms.<br>开关在接通和断开时的接点抖动时间不大于 10 ms.       |
| 6.MECHANICAL EFFICIENCY 机械性能  |                                    |                                                                                                                                                                      |                                                                                     |
| 6A                            | CONTACT STRENGTH<br>按键强度           | The contact shall be capable of a rorce of 5N for 5 seconds in any directions.沿开关动作方向可承受静能压力 5N, 保持 5 秒钟.                                                            | Switch electric andmechanical efficiency does not break 无损开关电气或者机械性能                |
| 6B                            | CONTACT JOURNEY                    |                                                                                                                                                                      | 按键行程<br>0.15 $\pm$ 0.05mm                                                           |
| 6C                            | DRIVE FORCE<br>驱动力                 | Being measure at across spring piece and across keystoke forergometer.<br>用测力计在按键与弹片之 间测量.                                                                           | Contact switch'sd drive dirive fouce was250 $\pm$ 30gf.<br>按键的开关驱动力为 250 $\pm$ 30gf |

|                                              |                                                                                                                                                                                                                                       |                                                                                                                                                                                         |                                                                                                                                              |
|----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|
| 6D                                           | CONNECTION<br>STRENGTH<br>接线端强度                                                                                                                                                                                                       | A force of 1N being applying in any directions of the switch connection partt..在接线端的作用方向施加 1N 的力.                                                                                       | Switch mechanical efficiency does not break.无损开关机械性能.                                                                                        |
| 6E                                           | MECHANICAL LIFE<br>机械寿命                                                                                                                                                                                                               | Operatin at a rate of 30-50 cycles a minute. 以 30-50 次/分的驱动速度操作.                                                                                                                        | Life50000cycles<br>寿命:50000次                                                                                                                 |
| 7.ENVIRONME NT----RESISTANT EFFICIENCY 耐环境性能 |                                                                                                                                                                                                                                       |                                                                                                                                                                                         |                                                                                                                                              |
| 7A                                           | CHANGE OF<br>TEMPERATURE 温度变化                                                                                                                                                                                                         | The first temperature shall be 70 °C ,3h and changed to-25°C, 0.5h, 5cycles of above test. 先 70°C, 3h, 然后-25°C, 0.5h, 如此重复 5 次.                                                         | 1. The appearance should not break.外观应无损伤.<br>2. Contact resistance $\leq 100\text{ M } \Omega$<br>接触电阻 $\leq 100\text{M } \Omega$           |
| 7B                                           | HUMIDITY RESISTANT<br>耐湿热                                                                                                                                                                                                             | 40 $\pm$ 2°C in temperature and 90-95%RH, Ruring thetest time without load; After testing the temperature should be 24h. 经 40 $\pm$ 2°C, 相对湿度 90-95%, 试验期间, 开关不动作, 不带电负荷, 试验后恢复到常温 24h. | 3. Insulation resistance $\geq 100\text{ M } \Omega$ .<br>绝缘电阻 $\geq 100\text{ M } \Omega$                                                   |
| 8.IOINTING EFFICIENCY 焊接性能                   |                                                                                                                                                                                                                                       |                                                                                                                                                                                         |                                                                                                                                              |
| 8A                                           | SOLDERABILITY<br>可焊性                                                                                                                                                                                                                  | Temperature260 $\pm$ 5 °C ;Duration;3 $\pm$ 0.5S:温度在 260 $\pm$ 5 °C, 持续 3 $\pm$ 0.5S.                                                                                                   | Solderability part should above 90%<br>可焊部分被焊料覆盖面应在 90% 以上.                                                                                  |
| 8B                                           | SOLDER—RESISTANT<br>耐焊剂性                                                                                                                                                                                                              | Warm-up temperature:100°C,40S, 焊锡温度 260 $\pm$ 5 °C, 浸焊时间 5 $\pm$ 0.5S.                                                                                                                  | Froth height of assist solder should under board and switch electric and mechanical efficien- cy does not break.助焊剂发泡不应超过印制板,无损伤开关电气或机械动作性能. |
| 8C                                           | JOINTING—RESISTANT<br>耐焊接热                                                                                                                                                                                                            | Jointing temperature: 260 $\pm$ 5 °C ,Duration of immersion: 5 $\pm$ 1S. 焊锡温度 260 $\pm$ 5 °C, 浸焊时间 5 $\pm$ 1S                                                                           | efficiency does not break 无损伤开关电气或机械动作性能.                                                                                                    |
| 8D                                           | NORMAL JOLNTING TIMES<br>正常焊接次数                                                                                                                                                                                                       |                                                                                                                                                                                         | $\leq 2$ times 小于 2 次                                                                                                                        |
| 9.NOTES                                      |                                                                                                                                                                                                                                       |                                                                                                                                                                                         |                                                                                                                                              |
| 9A                                           | The whole boxes of switch should keep in the temperature -30--80 °C and less than 80%RH withort acidic,alkalescence,caustic gas in the environment of the storage.<br>整箱包装的开关,应在温度为-30--80°C,相对湿度不大于 80%,周围的空气中没有酸性、碱性或其他腐蚀性气体的库房内保管。 |                                                                                                                                                                                         |                                                                                                                                              |
| 9B                                           | Operating Temperature Range:-20 to 70°C<br>操作温度的范围: -20 to 70°C                                                                                                                                                                       |                                                                                                                                                                                         |                                                                                                                                              |
| 9C                                           | Switch should install in a correct method.<br>开关应按正确的安装方法进行正确安装使用。                                                                                                                                                                    |                                                                                                                                                                                         |                                                                                                                                              |