



深圳市兴华鑫电子科技有限公司

Shenzhen xinghuaxin Electronic Technology Co., Ltd

承認書

SPECIFICATION FOR APPROVAL

客戶 (Customer):

客戶料號 (Customer P/N):

興華鑫型號 (Supplier P/N):

XHxDZ-3020BOX-1.25-L160

產品名稱 (Description):

喇叭 (Speaker)

產品規格 (Specification):

8Ω

客戶承認欄 (Customer Authorization Signature)	深圳市興華鑫電子科技有限公司 承認欄 (Supplier Audit)		
	審核	檢查	制作
	唐国兴	唐海兵	王前进
	日期: 2025 年 06 月 18 日 版次: A		

声音让生活更精彩!

地址: 深圳市宝安区新安街道新乐社区新乐路 88 号厂房四层

TEL: 0755-27892904

E-mail: jacky.tang@jsxhxdz.com

Http: www.jsxhxdz.com

深圳市兴华鑫电子科技有限公司


Model No.	3020BOX-1.25-L160	Date	2025-06-18	Page No.	1 / 6
產品規格內容 (SPECIFICATION)					
1.使用範圍 (Scope)					
此份規格書是針對多媒體產品內，所使用的微型揚聲器單體所提出的報告。					
This specification covers our product of miniature speaker unit for multimedia product.					
2.标准测试条件(Test condition)					
一般规格试验状态（特殊要求除外）：常温 5~35℃，常湿 45%~85%，气压 860~1060hPa.					
判定上有疑问时，试验状态为：温度 20±2℃，相对湿度 60%~70%，气压 860~1060 hPa.					
The test conditions unless otherwise specified should be normal temperature 5 to 35 ℃,Normal humidity 45 to 85% and normal atmospheric pressure 860 to 1060 hPa,However,if there arises a doubt in judgment,the test conditions shall be as follows:					
Temperature 20±2℃					
Humidity 60%~70%					
Atmosphere 860~1060 hPa					
3.電聲特性 (ELECTRO-ACOUSTIC CHARACTERISTICS)					
3.1 額定阻抗(Rated Impedance):					
8.0Ω ± 20% (AT 1.6K Hz ,1.0 Vrms)					
3.2 額定輸入功率(Rated Input Power)					
2.0 Watt (At 4.0Vrms white noise 96 Hours)					
3.3 最大輸入功率(Max. Input Power)					
2.5 Watt					
3.4 最低共振頻率(Resonant Frequency)					
1500Hz ± 20%					
3.5 輸出音壓(Output S.P.L)					
97± 3dB (0.1Watt , 0.1 Meter. Average at 0.8K,1.0K,1.5K,2.0K Hz)					
3.6 實效頻率範圍(Frequency Range)					
Fo ~ 20KHz (By Output S.P.L. -10dB)					
3.7 失真率(Distortion)					
Less than 5% (At 1.6KHz ,0.89Vrms)					
3.8 工作溫度(Operating Temperature)					
-25℃ ~ +65℃					
3.9 儲存溫度(Storage temperature)					
-25℃ ~ +65℃					
制 定	审 核	核 准	文 件 编 号		
王前进	唐海兵	唐国兴			

產品規格內容 (SPECIFICATION)

Model No.	3020BOX-1.25-L160	Date	2025-06-18	Page No.	2 / 6
-----------	-------------------	------	------------	----------	-------

4. 可靠性測試 (Reliability Test)

4.1 高低溫差循環測試(Temperature Cycling Test)



A	Low Temperature (-25°C±3°C)
B	High Temperature (+65°C±3°C)
C	Number of Cycle (3 Cycles)
D	Duration of Exposure 1 Hours, at Each Temperature Extremes
E	Duration of Recovery 1 Hours

4.2 抗濕度試驗(Humidity Test)

A	相對濕度(Relative Humidity)	90-95% at + 40°C ± 3°C
B	測試時間(Durations)	96 Hours
C	恢復時間(Durations of recovery)	6 Hours

4.3 連續負載測試(Load Test)

White Noise Without Weighted Filter 4.0 Volts.(RMS) 96 Hrs.

4.4 跌落試驗(Drop Test)

75 cm Free Falling On Concrete Floor, 10 Times.

4.5 異常音測試(Buzzes & Rattles)



Sine wave between at 3.0Vrms / 200~5000Hz

4.6 極性測試(Polarity test)

Diaphragm Shall Move Forward When Apply a Positive DC. Current to the “+”or “Marked” Terminal.


Model No.	3020BOX-1.25-L160	Date	2025-06-18	Page No.	3 / 6
-----------	-------------------	------	------------	----------	-------

5.測量方式 (Measurement Method)




Model No.	3020BOX-1.25-L160	Date	2025-06-18	Page No.	4/6
-----------	-------------------	------	------------	----------	-----

6. 頻率響應曲線圖(Frequency Response Curve)




7. 阻抗曲線圖(Impedance Curve)



Model No.	3020BOX-1.25-L160	Date	2025-06-18	Page No.	5 / 6
-----------	-------------------	------	------------	----------	-------

8. 喇叭外觀描述

(Unit:mm tolerance:±0.3)



產品規格內容 (SPECIFICATION)

Model No.	3020BOX-1.25-L160	Date	2025-06-18	Page No.	6/6
-----------	-------------------	------	------------	----------	-----

10.包裝示意圖(Packing Standard):

(Unit:cm tolerance:±3)

PACKING STANDARD:

