

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	04APR2019	RS	JO

- 1

0.00076[.000030] GOLD IN LOCALIZED PLATE AREA 0.00381[.000150] TIN-LEAD ON SOLDER TAILS ALL OVER 0.00127[.000050] NICKEL
- 2

USE 1.55±0.02[.0610±.0010] DRILLED HOLE (1.55mm DRILL). FINISH TO BE TIN/LEAD OVER 0.02[.001] MIN COPPER.
- 3

PLATING 0.0038 [.000150] TIN-LEAD OVER 0.00127 [.000050] NICKEL ON HOLDDOWN.
- 4

IF PLANNING TO USE MORE THAN ONE MATING PAIR OF CONNECTORS TO INTERCONNECT 2 BOARDS PLEASE REFER TO PARA. 3.3 IN THR APPLICATION SPEC, #114-7010.
- 5



PACKED IN TUBES.
- 6

HOUSING: LCP, COLOR-BLACK, CONTACT: COPPER ALLOY
HOLDDOWN: COPPER ALLOY
VACCUM COVER: ALLUMINIUM ALLOY
- 7




0.00076 [.000030] GOLD IN LOCALIZED PLATE AREA 0.00381 [.000150] TIN ON SOLDER TAILS ALL OVER 0.00127 [.000050] NICKEL.
- 8

PLATING 0.0038 [.000150] TIN OVER 0.00127 [.000050] NICKEL ON HOLDDOWN.
- 9


USE 1.55±0.02[.0610±.0010] DRILLED HOLE (1.55mm DRILL). FINISH TO BE TIN/LEAD OVER 0.02[.001] MIN COPPER.



SECTION A-A



7 8	65.28 [2.570]	67.97 [2.676]	63.91 [2.516]	49	100	6-2267254-0
7 8	52.93 [2.320]	61.62 [2.426]	57.55 [2.266]	44	90	5-2267254-9
7 8	52.58 [2.070]	55.27 [2.176]	51.21 [2.016]	39	80	5-2267254-8
7 8	46.23 [1.820]	48.92 [1.926]	44.86 [1.766]	34	70	5-2267254-7
7 8	39.88 [1.570]	42.57 [1.676]	38.51 [1.516]	29	60	5-2267254-6
7 8	33.53 [1.320]	36.22 [1.426]	32.16 [1.266]	24	50	5-2267254-5
7 8	27.18 [1.070]	29.87 [1.176]	25.81 [1.016]	19	40	5-2267254-4
7 8	20.83 [.820]	23.52 [.926]	19.46 [.766]	14	30	5-2267254-3
7 8	14.48 [.570]	17.17 [.676]	13.11 [.516]	9	20	5-2267254-2
7 8	8.12 [.320]	10.82 [.426]	6.75 [.266]	4	10	5-2267254-1
1 3	65.28 [2.570]	67.97 [2.676]	63.91 [2.516]	49	100	1-2267254-0
1 3	52.93 [2.320]	61.62 [2.426]	57.55 [2.266]	44	90	2267254-9
1 3	52.58 [2.070]	55.27 [2.176]	51.21 [2.016]	39	80	2267254-8
1 3	46.23 [1.820]	48.92 [1.926]	44.86 [1.766]	34	70	2267254-7
1 3	39.88 [1.570]	42.57 [1.676]	38.51 [1.516]	29	60	2267254-6
1 3	33.53 [1.320]	36.22 [1.426]	32.16 [1.266]	24	50	2267254-5
1 3	27.18 [1.070]	29.87 [1.176]	25.81 [1.016]	19	40	2267254-4
1 3	20.83 [.820]	23.52 [.926]	19.46 [.766]	14	30	2267254-3
1 3	14.48 [.570]	17.17 [.676]	13.11 [.516]	9	20	2267254-2
1 3	8.12 [.320]	10.82 [.426]	6.75 [.266]	4	10	2267254-1

FINISH		D		C		B		A		NUMBER OF POSITIONS		PART NUMBER			
THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN RAVI.S 04APR2019		CHK J.OLSON 04APR2019		 TE Connectivity					
DIMENSIONS: mm [INCH]		TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD J.OLSON 04APR2019		NAME							
		0 PLC ±				PRODUCT SPEC		ASSY, RECEPTACLE, VERT. DOUBLE ROW, THROUGH HOLE, AMPMODU 50/50 GRID CONNECTOR				SIZE		RESTRICTED TO	
		1 PLC ±				108-1332									
		2 PLC ±				APPLICATION SPEC									
		3 PLC ±0.13[.005]				114-7010									
MATERIAL		FINISH				WEIGHT		A1		CAGE CODE		DRAWING NO		2267254	
		-				-									
SEE TABLE						CUSTOMER DRAWING						SCALE		10:1	
												SHEET		1 OF 1	
												REV		A	