


REVISIONS						
P	LTR	DESCRIPTION			DATE	DWN
D	REVISED	PER	ECO	20-004365	2-4-21	CT

D

C

B

A



- CONNECTOR DIMENSIONS ARE PER ARINC 600 SPECIFICATION
- DUST COVER INSTALLED FOR SHIPPING. QTY = 2
- KEYING SHOWN IN POSITION "01" FOR REFERENCE ONLY. SEE TABLE FOR KEYING POSITION. FOR POSITION "00" KEYING SHIPPED UNASSEMBLED.
- ASSEMBLY SHOWN WITH DIE-CAST SHELL. ASSEMBLIES WITH MACHINED SHELLS MAY VARY SLIGHTLY IN APPEARANCE.

COMPONENT	MATERIAL	FINISH
SHELL	DIE CAST ALUMINUM PER ASTM-B-85 OR ASTM-B-211 6061-T6 OR ASTM-B-209 2024-T4/T351	ELECTROLESS NICKEL PER MIL-C-26074, CLASS 4, GRADE B
INSERT RETENTION PLATES	ALUMINUM ALLOY PER ASTM-B-209	ELECTROLESS NICKEL PER MIL-C-26074, CLASS 4, GRADE B
SCREWS	STEEL OR STAINLESS STEEL	PASSIVATED
POLARIZING POSTS	ZINC ALLOY PER ASTM-B-86	ELECTROLESS NICKEL PER MIL-C-26074, CLASS 4, GRADE B
POLARIZING POST RETAINING PLATE	ALUMINUM ALLOY PER ASTM-B-209	BLUE ANODIZED PER MIL-A-8625
ALL INSERTS	THERMOSET	—

"01"

MODULE A,B,D & E
208262-3 (#22 PIN CONTACT; QTY=600)
MODULE C & F
208273-2 (#12 SOCKET CONTACT; QTY=12)
208270-2 (#16 SOCKET CONTACT; QTY=6)
208267-2 (#20 SOCKET CONTACT; QTY=8)

2101253-1

KEYING POSITION

CONTACTS INCLUDED WITH CONNECTOR NOT INSTALLED

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN C.C.THOMAS 6-23-09
CHK K.THACKSTON 6-23-09
APVD K.THACKSTON 6-23-09

TE Connectivity

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± .005 [0.13]
1 PLC ± .005 [0.13]
2 PLC ± .005 [0.13]
3 PLC ± .005 [0.13]
4 PLC ± .005 [0.13]
ANGLES ± .005 [0.13]

NAME

PLUG ASSY, SIZE 3, ARINC 600 (150/150/13C2/150/150/13C2)

MATERIAL SEE TABLE

FINISH SEE TABLE

WEIGHT 0.000000

SIZE CAGE CODE DRAWING NO. A1 00779 C=2101253

RESTRICTED TO

CUSTOMER DRAWING

SCALE 1:1

SHEET 1 OF 1

REV D