

Han Coax ETCS-contact-female; D=7,5mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 001 6201
Specification	Han Coax ETCS-contact-female; D=7,5mm
HARTING eCatalogue	https://b2b.harting.com/09150016201

Identification

Category	Inserts
Series	Han [®] Coax ETCS
Description of the contact	for Han E [®] crimp contacts

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	1
further contacts	+ shielding
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 ... 5.5 mm ²
Rated current	16 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Impedance	50 Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
-------------------	--------------------



Pushing Performance

Material properties

Colour (insert)	RAL 7032 (pebble grey)
Material (shielding)	Zinc alloy
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Lead

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
----------------	-------------------------

Commercial data

Packaging size	1
Net weight	21.5 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors