




- NOTES
- ONE EXAMPLE OF THE ROTATION OF REF. NO. ①, ⑨ AND ⑩ IS SHOWN.
  - THE RECOMMENDED CLAMP TORQUE REF. NO. ⑩: 3 TO 4 N · m.  
LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ⑩ FROM LOOSENING.
  - ACRISSE FLATS HEXAGON HEAD OF REF. NO. ⑬: 1.27  
THE RECOMMENDED CLAMP TORQUE REF. NO. ⑬: 0.3 TO 0.4 N · m  
LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ⑬ FROM LOOSENING.
  - THIS PRODUCT TO BE USED WITH CABLECLAMP, JR13WCC-\*(72)  
\* DESIGNATE DIAMETER OF APPLICABLE CABLE.  
LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT FROM LOOSENING.
  - THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER,  
DEPENDING ON THE CABLE STRUCTURE.  
PLEASE CONFIRM BEFORE THE USE.

|                          |                                |                               |                               |                                |                                              |
|--------------------------|--------------------------------|-------------------------------|-------------------------------|--------------------------------|----------------------------------------------|
| 7                        | STEEL                          | NICKEL PLATING                | 13                            | STEEL                          | JISB1177 HEAGON SOCKET SET SCREW M2.6X0.45X2 |
| 6                        | BRASS                          | NICKEL PLATING                | 12                            | ACRYLONITRILE BUTADIENE RUBBER | (BLACK)                                      |
| 5                        | ACRYLONITRILE BUTADIENE RUBBER | (BLACK)                       | 11                            | PHOSPHOR BRONZE                | NICKEL PLATING                               |
| 4                        | BRASS                          | SILVER PLATING 2 $\mu$ m min. | 10                            | BRASS                          | NICKEL PLATING                               |
| 3                        | BRASS                          | SILVER PLATING 2 $\mu$ m min. | 9                             | BRASS                          | NICKEL PLATING                               |
| 2                        | POLYBUTYLENE TEREPHTHALATE     | (BLACK) UL94V-0               | 8                             | PHOSPHOR BRONZE                | NICKEL PLATING                               |
| 1                        | ZINC ALLOY                     | NICKEL PLATING                |                               |                                |                                              |
| NO.                      | MATERIAL                       | FINISH . REMARKS              | NO.                           | MATERIAL                       | FINISH . REMARKS                             |
| UNITS<br>mm              |                                |                               |                               |                                |                                              |
| SCALE<br>2 : 1           |                                | COUNT                         | DESCRIPTION OF REVISIONS      |                                |                                              |
| APPROVED : HY. KOBAYASHI |                                | 18.02.22                      | DRAWING NO. EDC-113405-31-00  |                                |                                              |
| CHECKED : HY. KOBAYASHI  |                                | 18.02.22                      | PART NO. HR22-12WTL P-20P(31) |                                |                                              |
| DESIGNED : HY. KISHI     |                                | 18.02.21                      | CODE NO. CL122-0054-5-31      |                                |                                              |
| DRAWN : MK. INOUE        |                                | 18.02.06                      |                               |                                |                                              |