

## Coaxial PCB Connector 85\_SMB-Z50-0-19/111\_N

### Description

Right angle PCB jack

Interface Standards

IEC 60169-10\_MIL-STD-348A/311\_CECC 22130

### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	4 GHz

#### Mechanical Data

Board mounting type	through holes
Weight	0.0021 kg

#### Environmental Data

Operating temperature	-40 °C to 100 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Zinc Alloy	SUCOPRO Plating
Body	Zinc Alloy	SUCOPRO Plating
Insulator	PFA / PTFE	

### Related Documents

Outline drawing	DOU-00013184
Catalogue drawing	DCA-00013186

### Ordering Information

Bulk 100 pcs package	85_SMB-Z50-0-19/111_NH
Single package	85_SMB-Z50-0-19/111_NE

### Remarks

PCB connector with stand-offs