



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H4	REVISED PER ECR-17-000959	24FEB2017	RS	DR
	H5	REVISED PER ECO-17-008808	07MAR2018	RS	DR



1	STAMP AMP 4W* APPROX AS SHOWN.
2	MAXIMUM LENGTH DOES NOT INCLUDE MANUFACTURING TABS.
3	MATERIAL: COPPER PER ASTM B152 ANNEALED.
4	TIN PLATE 0.00254 [.000100] MIN. EXT. THK. PER ASTM B545.
5	TIN/LEAD (60/40) PLATE, 0.00254 [.000100] MIN. EXT. THK. PER SAE-AMS-P-81728.
6	UL LISTED E13288, 4 AWG STRANDED.
7	CSA CERTIFIED LR7189, 4 AWG SOLID OR STRANDED.
8	NICKEL PLATE 0.00762[.000300] MIN. EXT. THK. PER SAE AMS QQ-N-290.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: SEE TABLE
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 16.8-26.7mm ² [33,100-52,600] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

PRELIMINARY	343°C [650°F]	----	100	LOOSE PIECE		34320-3
	170°C [338°F]	----	100	LOOSE PIECE		34320-1
		 	100	LOOSE PIECE		34320
	MAX. OPERATING TEMPERATURE	APPROVALS	QTY.	PACKAGE TYPE	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 4-14-93 CHK DA PATTERSON 4-14-93 APVD DA PATTERSON 4-14-93		 TE Connectivity Ltd.							
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME							
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -		SPLICE, PARALLEL, SOLISTRAND 4 AWG							
MATERIAL		FINISH		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
		SEE TABLE		A2		00779		G=34320		-	
CUSTOMER DRAWING								SCALE		10:1	
								SHEET		1 of 1	
								REV		H5	