

Coaxial Panel Connector 23_BNT-50-0-1/103_N

Description

Straight panel receptacle jack, flange mount

Interface standards
SUHNER-BNT



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	3 GHz

Mechanical Data

Number of matings	500
Weight	0.0111 kg

Environmental Data

Operating temperature	-50 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Bronze / Brass	Silver Plating
Body	Brass	SUCOPALATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00010388
Mounting hole	DOU-00009051

Ordering Information

Single package	23_BNT-50-0-1/103_NE
----------------	----------------------

Remarks

Triaxial Connector