




# 2 · ROW Cable to Board Horizontal SMT

.025"



**NM, NK**

9 thru 85 Contacts


NM-212-025-161-JCAC  
(METAL)



NK-2D2-025-225-TH00  
(METAL)



| SIZE | A     | B     | C     |       | D     | E    | F    | G    | J     | *HARDWARE    |
|------|-------|-------|-------|-------|-------|------|------|------|-------|--------------|
|      |       |       | PLUG  | RCPT  |       |      |      |      |       |              |
| 9    | .375  | .270  | .160  | .163  | .170  |      |      |      |       |              |
| 15   | .450  | .345  | .235  | .238  | .245  |      |      |      |       |              |
| 21   | .525  | .420  | .310  | .313  | .320  |      |      |      |       |              |
| 25   | .575  | .470  | .360  | .363  | .370  |      |      |      |       |              |
| 31   | .650  | .545  | .435  | .438  | .445  | .125 | .225 | .187 | .0575 | #0-80 THREAD |
| 37   | .725  | .620  | .510  | .513  | .520  |      |      |      |       |              |
| 51   | .900  | .795  | .685  | .688  | .695  |      |      |      |       |              |
| 65   | 1.075 | .970  | .860  | .863  | .870  |      |      |      |       |              |
| 69   | 1.125 | 1.020 | .910  | .913  | .920  |      |      |      |       |              |
| 85   | 1.377 | 1.246 | 1.110 | 1.113 | 1.120 | .150 | .270 | .210 | .0700 | #2-56 THREAD |



\* = #2-56 UNC THREAD ON 85 POSITION CONNECTORS.  
\*\* = 1/16" HEX ON 85 POSITION CONNECTORS. HEX MEASUREMENTS  
TAKEN ACROSS THE FLATS.