






NOTES:

CRIMPING:
USE CRIMP TOOL: 360X10409X
WITH TOOL INSERT: 360X20029X
SELECTOR SETTINGS: 5 FOR AWG 12
4 FOR AWG 14

plating	part no.
GOLD FLASH over NICKEL	132A11029X
30µin HARD GOLD over min. 50µin NICKEL	132C11029X
50µin HARD GOLD over min. 50µin NICKEL	132J11029X

RoHS compliant

STRIPPING DIMENSIONS



3	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED					
2	1	REAR SIDE	COPPER ALLOY	GOLD FLASH over NICKEL					
1	1	MATING SIDE	COPPER ALLOY	see table					
pos	qty	description	material	plating					
partlist									
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND		tolerance		 dim. in mm	scale:	5:1			
					material:	see notes			
						date	name	title: HIGH POWER CONTACT FEMALE CRIMP VERSION 20A D-SUB COMBINATION	
					drawn	26.07.06	Lehmenkühler		
					appd.	26.07.06	Kühle		
					norm				
		4 x c	Ä5997	22.02.16	K.H.	d-old	13K1IE8A/13K1A188A	dwg no:	DIN-A3
		2 x b	Ä3554	19.01.11	K.H.			13K1A1836	sh: 1
		a	Origin						
		rev.	description	date	name			part no:	 see table

part no: see table