


GU256X64C-D903M

SIMPLIFIED DATASHEET

■ Features

256x64 pixel graphic VFD
Module equips 16(8x2)
Capacitive Touch
Switches.
(Mutual Capacitive Type)

■ Outline dimensions



Get full specification



Click here to go to request form.

Specification

■ Electrical Ratings

Note: Logic input I/O is 3.3V C-MOS level.

Parameter	Symbo	Min.	Typ.	Max.	Unit	Condition
Power Supply Voltage	VCC	4.75	5.00	5.25	VDC	

■ Electrical Characteristic Please refer to a full specification for Characteristics of I/O ort.

Parameter	Symbo	Min.	Typ.	Max.	Unit	Condition
I2C Logic Input Current	IIH-1	-	-	1	uA	VIN=3.3V
SDA,SCL,/RESET	IIL-1	-	-	-0.5	mA	VIN=0V
I2C Logic Input Voltage	VIH-1	2.7	-	-	VDC	-
SDA,SCL,/RESET	VIL-1	-	-	0.6	VDC	-
I2C Logic Output Voltage S	VOL-1	-	-	0.8	VDC	IOL=2mA
I2C Logic Output Voltage	VOH-2	2.6	-	-	VDC	IOH=-0.5mA
MBUSY,/TRDY	VOL-2	-	-	0.9	VDC	IOL=1mA
Logic Input Current RxD	IIH-2	-	-	1	uA	VIN=3.3V
MOSI,SCK,/CS,HBUSY,/RESET	IIL-2	-	-	-0.5	mA	VIN=0V
Logic Input Voltage RxD	VIH-2	2.7	-	-	VDC	-
MOSI,SCK,/CS,HBUSY,/RESET	VIL-2	-	-	0.6	VDC	-
Logic Output Voltage	VOH-3	2.6	-	-	VDC	IOH=-0.5mA
TXD,MISO,MBUSY,/TRDY	VOL-3	-	-	0.9	VDC	IOL=1.0mA
Output permission current	IOH/L	-	-	±3	mA	Per port(8 I/O)
Power Supply Current	ICC-1	-	440	570	mADC	All dots turned on
	ICC-2	-	220	285	mADC	All dots turned off
	ICC-3	-	30	40	mADC	Display power off
Power consumption		-	2.2	2.85	W	All dots turned on

■ Optical characteristics

Parameters	
Luminance	300 cd/m ² Min. (600 cd/m ² Typ.)
Color of illumination	Green (Bluish green)

■ Physical Specification

Parameters	
Number of Dots	16,384 (256x64)
Active area (XxY)	83.08mm x 20.68 mm (X x Y)
Size of Dot (XxY)	0.2mm x 0.2mm (X x Y)
Pitch of Dot (XxY)	0.325 mm x 0.325 mm(X x Y)
Weight	approximately 67 g

■ Environmental Specification

Parameters	
Operating Temperature	-40 ~ +85°C
Storage Temperature	-40 ~ +85°C
Operating Humidity	20 ~ 80% R.H. (non-condensing)
Storage Humidity	20 ~ 80% R.H. (non-condensing)
Vibration (non-operating)	10-55-10Hz, all amplitude 1mm, 30 minutes, X-Y-Z
Shock (non-operating)	392m/s ² (40G) 9ms X-Y-Z, 3 times each direction

■ Host Interface

Asynchronous Serial, SPI and I2C (Logic level is 3.3V for all)

■ Pin Assignment

CN2: Asynchronous Serial

Pin No.	Signal	Pin No.	Signal
1	VCC	8	TXD
2	RXD	9	/TRDY
3	GND	10	GND
4	MBUSY	11	P00
5	IC	12	P01
6	/RESET	13	P02
7	HBUSY	14	P03

CN2 : SPI Interface

Pin No.	Signal	Pin No.	Signal
1	VCC	8	MISO
2	MOSI	9	/TRDY
3	GND	10	GND
4	MBUSY	11	P00
5	SCK	12	P01
6	/RESET	13	P02
7	/CS	14	P03

CN2 : I2C Interface

Pin No.	Signal	Pin No.	Signal
1	VCC	8	IC
2	SDA	9	/TRDY
3	GND	10	GND
4	MBUSY	11	P00
5	SCL	12	P01
6	/RESET	13	P02
7	IC	14	P03

■ Character Fonts

Parameters	
Font tables	5 x 7 Alpha-numeric, Kana, International
	8 x 16 Alpha-numeric, Kana, International
	16 x 16 CJK
Number of digits & lin	5x7 dot font: 36/42digits x 8 lines(Fixed width)
	16x16 dot font: 16digits x 4line

■ Functions

Characters and Graphics display, Control command,
Macro & P Macro, I/O port,
Touch Switch with Calibration, etc.

