







SCALE 2:1



COMPANY LOGO



SHIELD HOUSING


44.6 REF
LEVER HEIGHT

36.0 REF


44.3
REF

12.5


LEVER
DELIVERY CONDITION WITH LEVER
SHOWN LOCKED IN UNMATED POSITION



KEY C SHOWN



KEY B SHOWN




KEY A SHOWN


KEYING OPTIONS
REFERENCE ONLY

- ⚠ MATERIAL: SHIELD - 35% GLASS REINFORCED NYLON,
SEE TABLE BELOW FOR COLOR.
LEVER - 35% GLASS REINFORCED NYLON, COLOR GRAY.
- REFERENCE: RECEPTACLE HOUSING 1326227-1
USED WITH THIS ASSEMBLY.
 - REFER TO INSTRUCTION SHEET 408-8662 FOR PRODUCT
ASSEMBLY AND DISASSEMBLY PROCEDURES.
 - REFER TO USCAR-2 REV 3 APRIL 2001 FOR PRODUCT
SPECIFICATIONS.
 - REFER TO DRAWING NO. AUAUT00000-2962-0486 FOR
INTERFACE DETAILS.


LOC		DIST		REVISIONS					
FX		00		P	LTR	DESCRIPTION	DATE	OWN	APVD
					0	RELEASED PER EC# 0K80-0283-02	20DEC2002	SPT	AME
					A	REV PER EC 0K80-0113-03	16APR2003	RGV	AME
					A1	REV PER ECR-10-011823	28MAY2010	VSS	CS



70° WIRE EXIT
SCALE 2:1



45° WIRE EXIT
SCALE 2:1





20° WIRE EXIT
SCALE 2:1

WIRE EXIT OPTIONS
REFERENCE ONLY



70°	BLACK	A	I-1326226-0
20°	BLACK	C	1326226-9
20°	BLUE	B	1326226-8
20°	GREY	A	1326226-7
45°	BLACK	C	1326226-6
45°	BLUE	B	1326226-5
45°	GREY	A	1326226-4
70°	BLACK	C	1326226-3
70°	BLUE	B	1326226-2
70°	GREY	A	1326226-1
DIM W	COLOR	KEYING OPT.	PART NUMBER

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN W. HOELSCHER 04SEP2001		Tyco Electronics	
mm		0 PLC ±.1		CHK S. TOBEY 04SEP2001		Tyco Electronics	
0 PLC ±.2		1 PLC ±0.05		APVD S. TOBEY 04SEP2001		Harrisburg, PA 17105-3608	
2 PLC ±.1		3 PLC ±.1		PRODUCT SPEC		NAME	
4 PLC ±.1		5 PLC ±.1		APPLICATION SPEC		SHIELD ASSEMBLY	
6 PLC ±.1		7 PLC ±.1		WEIGHT		32 POSITION	
8 PLC ±.1		9 PLC ±.1		CUSTOMER DRAWING		0.64mm LAC	
FINISH		RESTRICTED TO		SIZE		CAGE CODE	
DRAWING NO		DRAWING NO		00779		C=1326226	
SCALE		SHEET		OF		REV	
3:1		1		2		A1	


LOC		DIST		REVISIONS			
F	LYR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	




SCALE 3:1




SECTION W-W




DETAIL X
SCALE 4:1



KEY OPTION A



KEY OPTION B



KEY OPTION C

KEYING OPTIONS

- CONNECTOR FIXTURE SHOULD BE USED TO VERIFY THE RECEPTACLE CARRIER IS PROPERLY SEATED AND LOCKED INTO THE SHIELD ASSEMBLY. THE CONNECTOR WILL NOT FULLY MATE TO THE FIXTURE IF THE RECEPTACLE CARRIER IS OUT OF POSITION.
- RECOMMEND USING A SENSING DEVICE FOR VERIFYING FULLY MATED CONNECTORS. SUCH A DEVICE IS UP TO THE CUSTOMERS DISCRESSION.
- RECOMMENDED MATERIAL: HARDEND STEEL
- NO RADII OR CHAMFER PERMITTED IN SPECIFIED AREA. MUST MAINTAIN 90° EDGE.
- RADII TO BE 0.5 UNLESS OTHERWISE SPECIFIED.
- OPTIONAL CONSTRAINT FEATURE.

TYPICAL DIMENSIONS TO CENTERLINE UNLESS OTHERWISE SPECIFIED		DWN W. HOELSCHER CHK S. TOBEY APVD S. TOBEY		04SEP2001 04SEP2001 04SEP2001		Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		NAME	
mm		0 PLC ±.1 1 PLC ±0.2 2 PLC ±0.05 3 PLC ±.1 4 PLC ±.1		APPLICATION SPEC		SIZE	
MATERIAL		FINISH		WEIGHT		CAGE CODE	
3		-		-		00779	
CUSTOMER DRAWING		SCALE		SHEET		REV	
		5:2		2		A1	