

Molded Parts
Specification Control Drawing

Part Number : 293A100
Description : Boot, Rectangular,
MTC Connector

- NOTES
1. All dimensions are in inches / millimeters
2. Dimensions appearing in table are as follows:
a - As Supplied
b - After Unrestricted Recovery
3. Coating is required. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.




TABLE OF DIMENSIONS

PART NUMBER	H		J		K		P	R	JO	W
	Min a	Max b	Min a	Max b	Min a	Max b	±10% b	±10% b	±10% b	±20% b
293A100	2.43 [61,7]	2.32 [58,9]	1.20 [30,5]	.59 [15,0]	1.20 [30,5]	.26 [6,6]	4.25 [108,0]	1.00 [25,4]	1.35 [34,3]	.06 [1,5]

If this document is printed it becomes uncontrolled.
Check for the latest revision.

Revision : B
Date : 7/28/04

Part Number : 293A100
Description : Boot, Rectangular,
MTC Connector

Molded Parts
Specification Control Drawing

Part Number : 293A100
Description : Boot, Rectangular,
MTC Connector

COMPATABILITY CHART

MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-25	Elastomer, Fluid Resistant	RT-1325	/86	S-1048	Adhesive

ORDERING INFORMATION

293A100 -25 -XX /86 -0

Base part number _____

Material dash number _____

(See Compatability Chart)

Modification number _____

Adhesive slash number _____

(If necessary, see Compatability Chart)

Color Designator _____

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

Revision : B
Date : 7/28/04

Part Number : 293A100
Description : Boot, Rectangular,
MTC Connector