




- NOTES
- 1 THE RECOMMENDED CLAMP TORQUE OF REF.NO.⑪ : 1 N · m.
LOCTITE 271, HENKEL JAPAN IS RECOMMENDED TO REF.NO.⑪ FROM LOOSENING.
 - 2 ROTATION EXAMPLES OF REF.NO. ① AND ⑪ ARE SHOWN.
 - 3 B DIMENSION IS FOLLOWING. CONTACT NO. 1 : (1.5)
CONTACT NO. 2 TO 6 : (3)
 - 4 SURFACE PLATING : GOLD PLATING 0.2 μm min.
UNDER PLATING : NICKEL PLATING 3 μm min.
 - 5 Fig.1 REPRESENTS THE PRODUCT APPEARANCE AFTER IMPROPER ASSEMBLY.
IF THE LOCK GROOVE IS VISIBLE, NO.① AND NO.⑪ MAY NOT BE ASSEMBLED CORRECTLY.

6	BERYLLIUM COPPER	NICKEL PLATING	12	SIR	(BLACK)
5	PHOSPHOR BRONZE	TIN PLATING	11	BRASS	NICKEL PLATING
4	PBT	(BLACK) UL94V-0	10	POLYACETAL	
3	BRASS	④	9	STEEL	NICKLE PLATING
2	BRASS	④	8	BRASS	MATTE FINISH NICKEL PLATING
1	ALUMINUM ALLOY	NICKEL PLATING	7	STAINLESS STEEL	
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 4 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-C-00005509	DESIGNED KN. IKEHARA
		APPROVED : MR. YOSHIDA	20050105	DRAWING NO.	EDC3-110281-71
		CHECKED : MO. SATOH	20050105	PART NO.	MXR-8PA-6PB(71)
		DESIGNED : YH. YAMADA	20050105	CODE NO.	CL0127-0005-1-71
		DRAWN : YH. YAMADA	20050105		
		DATE	20210325		