


D


C

B


A





SINGLE POLARIZATION



DOUBLE POLARIZATION



THREE KEY POLARIZATION




D

C


B

A

- 1 THE PART IS MARKED WITH THE TE PART NUMBER, CHINA, DATE CODE AND LOT ID.
2. DWV RATING: 725VAC @ SEA LEVEL
3. WORKING TEMPERATURE: -55°C ~ +125°C
- 4 MATERIAL:
CONTACT : COPPER ALLOY
SHELL : COPPER ALLOY
INSULATOR : PEEK
O RING : SILICON RUBBER
- 5 FINISH
CONTACT: GOLD OVER NICKEL
SHELL : BLACK CHROMIUM
6. WATER PROOF: 1M IMMERSION.
- 7 ALL TOLERANCES TO BE ±0.20MM UNLESS NOTED.



CAVITY IDENTIFICATION WHEN VIEWED FROM REAR OF CONNECTOR



PANEL CUTOUT

CHROMIUM-BLACK	THREE	SOLDERING	2.54	Ø0.5	15.45	Ø14	M14X1	Ø18	2	2157375-3
CHROMIUM-BLACK	DOUBLE	SOLDERING	2.54	Ø0.5	15.45	Ø14	M14X1	Ø18	2	2157375-2
CHROMIUM-BLACK	SINGLE	SOLDERING	2.54	Ø0.5	15.45	Ø14	M14X1	Ø18	2	2157375-1
FINISH	POLARIZATION	TERMINATION	N	d	L	T	M THREAD	D	SHELL SIZE	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

4

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	0.20
3 PLC	±	-
4 PLC	±	-
ANGLES	±	3°

FINISH

5

DWN
C.C THOMAS
24FEB2011

CHK
R. GROSS
24FEB2011

APVD
R. GROSS
24FEB2011

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

CIRCULAR HD RECEPTACLE WITH SOCKET CONTACTS
JAM NUT, FRONT MOUNTING, STRAIGHT PCB

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C=2157375	-

SCALE	SHEET	REV
NTS	1 OF 1	C