



LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B2	REVISED PER ECR-21-123979	17DEC2021	PC	KR



- MAGNET WIRE: #18 - 34 AWG, 1.02[.040] - 0.16[.006] DIA COPPER. OTHER SIZES MAY BE ACCOMMODATED, CONSULT TYCO ELECTRONICS FOR APPROVAL.
 - POCKET RECOMMENDATION: #1601425 EXCEPT ONLY 7.87 [.310] DEEP
- 3 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS APPLICATION SPECIFICATION 114-13166 FIGURE 7.
- 4 PRE-PRODUCTION- FASR REQUIRED.

OBSOLETE	POST TIN OVER NICKEL PLATE	-	4	4-1601088-4
	POST TIN OVER NICKEL PLATE	-	4	1601088-4
	PRE TIN PLATE	031-159-002		4-1601088-2
	PRE TIN PLATE	131-160-002		2-1601088-2
	PRE TIN PLATE	131-159-002		1601088-2
	FINISH	REFERENCE PART NUMBER		TE PART NUMBER
	THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN J.WELLER 11JAN2002 CHK M.FEHER 11JAN2002 APVD K.RANDOLPH 11JAN2002	NAME	
	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± 2°	PRODUCT SPEC 108-2085 APPLICATION SPEC	
	MATERIAL BRASS, SPRING HARD	FINISH SEE TABLE	WEIGHT -	SCALE 8:1
			CUSTOMER DRAWING	SHEET 1 OF 1
				REV B2