

**447162-1**

✓ ACTIVE


**AMP**

TE Internal #: 447162-1

Dust Cover, Caplugs Conductive Material

[View on TE.com >](#)

Connectors &gt; Connector Accessories &gt; Connector Caps &amp; Covers

Connector Cover Type: **Dust Cover**Primary Product Material: **Caplugs Conductive Material**Operating Temperature (Max): **125 °C [ 257 °F ]**Operating Temperature Range: **-65 – 125 °C [ -85 – 257 °F ]**

## Features

### Product Type Features

Connector Cover Type

Dust Cover

### Body Features

Primary Product Material

Caplugs Conductive Material

### Usage Conditions

Compatible With Connector Style

Plug

Operating Temperature (Max)

125 °C[257 °F]

Operating Temperature Range

-65 – 125 °C[-85 – 257 °F]

### Packaging Features

Packaging Method

Package

## Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2024 (240)

Candidate List Declared Against: JAN 2024 (240)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I &lt; 900 ppm per homogenous material. Also BFR/CFR/PVC

Free

Solder Process Capability

Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Customers Also Bought



TE Part #1658641-1  
HDP-20, PLUG, SIZE 5, 50 POSN



TE Part #1053635-1  
2081 0000 02



TE Part #1617754-2  
FCA-410-1521M=M83536/15-021M



TE Part #YDTS24W15-35SNV001  
RECP ASSY



TE Part #YDTS26W17-35SAV001  
PLUG ASSY



TE Part #YDTS20F25-61PNV001  
RECP ASSY



TE Part #YDTS24F25-35PAV001  
D38999: Jam Nut, 25-35 Insert,  
Electroless Nickel Plating



TE Part #YDTS26W25-35SBV001  
PLUG ASSY



TE Part #87667-1  
MOD IV RECP LP

## Documents

## Datasheets &amp; Catalog Pages

[ARINC 600 Next Generation Receptacle Connector](#)

English