


D

C

B

A



- 1

POLYOLEFIN, BLACK.
- 2

NYLON, BLACK.
- 3

NOMINAL WALL THICKNESS, EXPANDED.
- 4

LENGTH OF SEALANT.
- 5

EXPANDED INSIDE DIAMETER.
- 6

6.35[.250] MAXIMUM RECOVERED INSIDE DIAMETER.
- 7

ASSEMBLY WILL PASS 0.0703 KG PER SQ CENTIMETER [ONE POUND PER SQ IN.] WATER PRESSURE TEST.
- 8

121°C [250°F] SHRINK TEMPERATURE.
- 9

-55°C TO 110°C [-67°F TO 230°F] OPERATING TEMPERATURE.
- 10

THIS PART WILL ACCOMODATE ø6.35 - ø15.24 [ø.250 - ø.600] CABLE RANGE.
- 11

4.06 [.160] MAXIMUM RECOVERED INSIDE DIAMETER.
- 12

ACTUAL SHAPE MAY VARY DUE TO PROCESS VARIANCE.
- 13

SEE P/N CHART FOR MARKING. WHITE CHARACTERS .150 MIN HIGH AND LOCATED ON THE OUTSIDE SURFACE OF THE TUBING.
- 14

OBSOLETE PART.

TE 54010-5	6 8	2.25	14 54010-5
NONE	11 8	2.25	54010-4
NONE	6 8	1.25	54010-2
NONE	6 8	2.25	54010-1
MARKING	RECOVERED INSIDE DIS	A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C.REIFSNYDER
09 APR 96

CHK
R.STONE
15 APR 95

APVD
T.A.WETZEL
03 MAY 96

TE Connectivity

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH	-	-

MATERIAL
TUBING:

1

SLEEVE:

2

WEIGHT

-

CUSTOMER DRAWING

SCALE 2:1

SHEET 1 of 1

REV AD

NAME
STRAIN RELIEF ASSY,
SHELL SIZE 11, CPC

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=54010

RESTRICTED TO
-