

## Coaxial PCB Connector 85\_BNC-50-0-1/133\_N

### Description

Right angle PCB jack

Interface Standards

IEC 60169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	4 GHz

#### Mechanical Data

Board mounting type	through holes
Weight	0.0187 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

### Related Documents

Outline drawing	DOU-00070952
Catalogue drawing	DCA-00012658
Mounting hole	DOU-00012084

### Ordering Information

Single package	85_BNC-50-0-1/133_NE
----------------	----------------------

### Remarks

PCB connector with stand-offs