




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		C	REVISED PER ECO-15-011840	17NOV15	RS	CT

D

C


B

A



1218638-1 SHOWN

- TE PART NO. AND DESCRIPTIVE PART NO. MARKED IS THIS AREA.
- "AMP" AND DATE CODE MARKED IN THIS AREA.
- KEYING ASSEMBLED IN THE "01" POSITION.
- MATERIAL AND FINISH:
SHELL: DIE CAST ALUMINUM ALLOY PER SPEC QQ-A-591.
STANDARD FINISH: CADMIUM PLATE PER QQ-P-416, TYPE I, CLASS 2 YELLOW CHROMATE CONVERSION.
INSERT RETENTION PLATE: ALUMINUM ALLOY, BLUE ANODIZE PER MIL-A-8625.
SCREWS AND WASHERS: STAINLESS STEEL, PASSIVATED.
POLARIZING POSTS: STAINLESS STEEL, PASSIVATED.
POLARIZING NUTS: BRASS, CADMIUM PLATED.
- KEYING POSTS NOT ASSEMBLED AND PACKAGED SEPARATELY. (-2 & -3)
- 1218638-2 SUPPLIED WITH 59 SIZE 20 SOCKET CONTACTS.
- 1218638-3 SUPPLIED WITH 66 SIZE 20 SOCKET CONTACTS.



OBSOLETE	5 7	M1P67S-00 (206)	1218638-3
OBSOLETE	5 6	M1P57S-00 (206)	1218638-2
		MME1P57P-2301 (204)	1218638-1
REMARKS		DESCRIPTIVE NO.	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 3-13-14	TE Connectivity			
DIMENSIONS: INCHES		CHK D.EABY 3-13-14				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D.EABY 3-13-14	NAME CONNECTOR ASSY,ARINC 404			
MATERIAL		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO			
FINISH		APPLICATION SPEC	A2 00779 C=1218638			
		WEIGHT	SCALE 2:1 SHEET 1 of 1 REV C			
		CUSTOMER DRAWING				