


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECR-20-100406	16SEP2020	WH	DZ

- 1
- HOUSING MATERIAL: NYLON, UL94 V0.
PIN MATERIAL: BRASS.
- 2
- PIN PLATING: 0.003 [.000120] MIN TIN OVER 0.001 [.000039] NICKEL.
- 3
- COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30 (GWT).
- 4
- SKETCHES SHOW NO PINS MISSING.
- 5
- "O" WITH POST, "X" WITHOUT POST
- 6
- PRODUCT BOW SHOULD MEET 0~0.08MM(INITIAL) AND 0~0.20MM(AFTER SOLDERABILITY)



O	X	O	X	O	O	O	O					8	31.68 [1.247]	1-1744524-8
O	X	O	O	O	O	O	O	O				9	35.64 [1.403]	4-1744524-9
O	O	O	O	O	X	O	O	O				9	35.64 [1.403]	3-1744524-9
O	X	O	O	O	O	O	O	O	O	O		11	43.56 [1.715]	2-1744524-1
O	X	X	O									4	15.84 [0.624]	2-1744524-4
O	O	X	O									4	15.84 [0.624]	1-1744524-4
O	O	X	O	O	X	O	O					8	31.68 [1.247]	1744524-8
O	O	X	O	O								5	19.80 [0.780]	4-1744524-5
O	X	O	X	O	O	X	O	O				9	35.64 [1.403]	2-1744524-9
O	O	O	X	O								5	19.80 [0.780]	3-1744524-5
O	X	X	X	O								5	19.80 [0.780]	2-1744524-5
O	X	O	X	X	O							6	23.76 [0.935]	1-1744524-6
O	O	X	X	O								5	19.80 [0.780]	1-1744524-5
O	O	O	X	O	X	O						7	27.72 [1.091]	7-1744524-7
O	X	O										3	11.88 [0.468]	4-1744524-3
O	X	O	X	O	X	O	X	O				9	35.64 [1.403]	1-1744524-9
O	X	O	X	O	X	O						7	27.72 [1.091]	8-1744524-7
O	X	O	X	O	X							6	23.76 [0.935]	8-1744524-6
O	X	O	X	O	O							6	23.76 [0.935]	7-1744524-6
O	O	X	O	X	O							6	23.76 [0.935]	6-1744524-6
O	O	O	O	X	O							6	23.76 [0.935]	4-1744524-6
O	X	O	O	O	O							6	23.76 [0.935]	2-1744524-6
O	O	O	O	O	O	X	O	O				9	35.64 [1.403]	1744524-9
O	X	O	O	O	O	O						7	27.72 [1.091]	1744524-7
O	O	O	X	O	O							6	23.76 [0.935]	1744524-6
O	X	O	X	O								5	19.80 [0.780]	1744524-5
O	X	O	O									4	15.84 [0.624]	1744524-4
1	2	3	4	5	6	7	8	9	10	11	12	NO. OF POSITIONS	±0.30 [.012] DIM A	PART NUMBER

RECOMMENDED MOUNTING HOLE PATTERN FOR 1.60 [.063] THICK PC BOARD

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± 0.5[.02]
2 PLC	± 0.30[.012]
3 PLC	± -
4 PLC	± -
ANGLES	± -

FINISH

DWN
JR RUTH

CHK
TOM MICHELUTTI

APVD
TOM MICHELUTTI

PRODUCT SPEC
108-5609

APPLICATION SPEC
114-32134

WEIGHT
-

CUSTOMER DRAWING

20MAR13

20MAR13

20MAR13

NAME
TE Connectivity

HEADER ASSEMBLY-ECONOMY POWER VERTICAL

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1744524

RESTRICTED TO
-

SCALE
N/A

SHEET
1 of 1

REV
D1