





LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	DWN
			D2	REVISED PER ECR-10-006140	07APR10	HMR
						APVD
						GJ



- 1 SPECIFICATIONS: MAGNET WIRE #18-#34 AWG, 1.02[.040]-0.16[.006] DIA COPPER.
- 2 POCKET RECOMMENDATION: 1601425.
- 3 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS SPECIFICATION 114-13166 FIGURE 9.
- 4 THIS LENGTH TO BE COINED AND FREE OF BURRS.
- 5 PRELIMINARY - NOT FOR PRODUCTION.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 7 TWO (2) TERMINALS SHOWN FOR ILLUSTRATION PURPOSES ONLY.



6 OBSOLETE

PRE-TIN PLATE	5 4-1601179-2
PRE-TIN PLATE	2-1601179-2
PRE-TIN PLATE	1601179-2
FINISH	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MICHAEL S. FEHER 24MAR2003 CHK GENE JACONO 25MAR2003 APVD GENE JACONO 25MAR2003		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± -		STD RANGE WIRE TO 2.8 x 0.8	
		1 PLC ± -		MULTI-BARB TAB SIAMEZE TERMINAL	
		2 PLC ± 0.13[.005]		-	
		3 PLC ± -			
4 PLC ± -		PRODUCT SPEC			
ANGLES ± 2°		APPLICATION SPEC			
MATERIAL		WEIGHT		SIZE	
BRASS, 3/4 HARD		-		A2 00779	
SEE TABLE		CUSTOMER DRAWING		DRAWING NO	
				C=1601179	
				RESTRICTED TO	
				-	
				SCALE	
				6:1	
				SHEET	
				1 of 1	
				REV	
				D2	