

Series 800 Mighty Mouse, UN Mating Thread PCB Mount Right Angle Header Receptacle

800-032 Ordering Information



Series 800



Printed Circuit Board Right Angle I/O Header features gold-plated size #23 contacts. UN mating thread, and aluminum or stainless steel shells. Rubber seal protects mated connectors from water ingress. 5 amp current rating, 500 VAC voltage rating. Contacts are factory-installed and are non-removable. Thermoplastic rear housing has #2-56 threaded inserts for attaching to circuit board with customer-supplied mounting screws. Connectors attach to chassis or panel with low-profile jam-nut and O-ring. Available in six contact arrangements, these right angle headers are ideal for hostile environments where 100/100BASE-T Ethernet RJ-45 commercial-grade jacks are not advised.

How To Order						
Sample Part Number		800-032	-07	M	7-10	P Z
Series	800-032 PCB Receptacle					
Shell Style	-07 = Jam-Nut					
Shell Material and Finish	C = Aluminum / Black Anodize (Non-Conductive) RoHS Compliant M = Aluminum / Electroless Nickel RoHS Compliant NF = Aluminum / Cadmium with Olive Drab Chromate ZNU = Aluminum / Zinc-Nickel with Black Chromate MT = Aluminum / Nickel-PTFE RoHS Compliant Z1 = Stainless Steel / Passivated RoHS Compliant					
Shell Size - Insert Arrangement	5-3, 6-1, 6-4, 6-6, 6-7, 7-1, 7-10, 8-2, 8-13, 9-4, 9-19, 9-200, 10-2, 10-5, 10-201					
Contact Type	P = Pin, PC Tail S = Socket, PC Tail					
Shell Key Position (See Table I)	N = Normal X = Pos. X Y = Pos. Y Z = Pos. Z					




Table I: Shell Keyway Positions			
Keyway Position	Keyway Rotation	Shell Size 5 and 6	Shell Size 7 thru 12
N Normal	150°		
X	140°		
Y	130°		
Z	120°		
Shell sizes 5 thru 6 and insert arrangement 8-13: master key is located at top dead center for normal (N) position. Shell size 7 thru 12: master key is rotated 90° from TDC for normal position			

Dimensions in Inches (millimeters) are subject to change without notice.



Series 800 Mighty Mouse, UN Mating Thread PCB Mount Right Angle Header Receptacle 800-032 Dimensions

Jam-nut mount receptacle - shell style 07



Material / finish:

- Receptacle shell, jam-nut: aluminum alloy or CRES / see How to Order Table
- Insulator: LCP or epoxy / N.A.
- Interfacial seal, O-ring: fluorosilicone
- Contact: copper alloy / gold plate per ASTM B 488, Type II, Class 1.25, over a suitable underplate
- Potting: epoxy

Dimensions											
Size - Arr	A Flat ±.005 (±0.13)	B Flat	Ø C	D Threads	E	F	G ±.035 (±0.89)	H ±.005 (±0.13)	J	K	L
5-3	.282 (7.16) .291 (7.39)	.497 (12.62)	.538 (13.67)	.3125-28 UN-2A	.260 (6.60)	.235 (5.97)	.257 (6.53)	.050 (1.27)	.165 (4.19)	.310 (7.87)	.49 (12.45)
6-1		.559 (14.20)	.602 (15.29)	.3750-28 UN-2A	.350 (8.89)	.225 (5.72)	.285 (7.24)	.050 (1.27)	.224 (5.69)	.385 (9.78)	.58 (14.73)
6-4	.350 (8.89) .359 (9.12)	.559 (14.20)	.602 (15.29)	.3750-28 UN-2A	.330 (8.38)	.225 (5.72)	.285 (7.24)	.050 (1.27)	.224 (5.69)	.385 (9.78)	.58 (14.73)
6-6,6-7		.559 (14.20)	.602 (15.29)	.3750-28 UN-2A	.350 (8.89)	.225 (5.72)	.285 (7.24)	.050 (1.27)	.187 (4.75)	.408 (10.36)	.58 (14.73)
7-1	.409 (10.39)	.643 (16.33)	.664 (16.87)	.4375-28 UNEF-2A	.350 (8.89)	.296 (7.52)	.200 (5.08)	.092 (2.34)	.170 (4.32)	.452 (11.48)	.71 (18.03)
7-10	.418 (10.62)	.643 (16.33)	.664 (16.87)	.4375-28 UNEF-2A	.350 (8.89)	.296 (7.52)	.274 (6.96)	.092 (2.34)	.170 (4.32)	.452 (11.48)	.71 (18.03)
8-2	.471 (11.96)	.731 (18.57)	.770 (19.56)	.5000-28 UN-2A	.490 (12.45)	.320 (8.13)	.336 (8.53)	.092 (2.34)	.230 (5.84)	.490 (12.45)	.71 (18.03)
8-13	.480 (12.19)	.731 (18.57)	.770 (19.56)	.5000-32 UN-2A	.490 (12.45)	.320 (8.13)	.315 (8.00)	.092 (2.34)	.230 (5.84)	.490 (12.45)	.71 (18.03)
9-4		.803 (20.40)	.872 (22.15)	.5625-28 UN-2A	.490 (12.45)	.362 (9.19)	.288 (7.32)	.092 (2.34)	.342 (8.69)	.600 (15.24)	.80 (20.32)
9-19	.528 (13.41)	.803 (20.40)	.872 (22.15)	.5625-32 UN-2A	.490 (12.45)	.362 (9.19)	.283 (7.19)	.092 (2.34)	.342 (8.69)	.600 (15.24)	.80 (20.32)
9-200	.537 (13.64)	.803 (20.40)	.872 (22.15)	.5625-28 UN-2A	.490 (12.45)	.362 (9.19)	.240 (6.10)	.092 (2.34)	.342 (8.69)	.600 (15.24)	.80 (20.32)
10-2		.940 (23.88)	.976 (24.79)	.6250-28 UN-2A	.570 (14.48)	.397 (10.08)	.272 (6.91)	.092 (2.34)	.362 (9.19)	.640 (16.26)	.84 (21.34)
10-5	.602 (15.29)	.940 (23.88)	.976 (24.79)	.6250-28 UN-2A	.570 (14.48)	.397 (10.08)	.305 (7.75)	.092 (2.34)	.362 (9.19)	.640 (16.26)	.84 (21.34)
10-201	.611 (15.52)	.940 (23.88)	.976 (24.79)	.6250-28 UN-2A	.570 (14.48)	.397 (10.08)	.272 (6.91)	.092 (2.34)	.362 (9.19)	.640 (16.26)	.84 (21.34)



Dimensions in Inches (millimeters) are subject to change without notice.

Series 800 Mighty Mouse, UN Mating Thread PCB Mount Right Angle Header Receptacle 800-032 Dimensions





Series 800




C

Panel Cutouts for Right Angle PCB Headers		
	ShellSize	A Flat ϕB
 RECOMMENDED PANEL CUTOUTS EXCEPT 8-13	5	.299 (7.59) .295 (7.49)
	6	.362 (9.19) .358 (9.09)
 RECOMMENDED PANEL CUTOUT FOR 8-13	7	.428 (10.87) .424 (10.77)
	8	.483 (12.27) .479 (12.17)
	9	.541 (13.74) .537 (13.64)
	10	.541 (13.74) .537 (13.64)

FACE VIEW AND KEYWAY POSITION OF RIGHT ANGLE PCB HEADERS



Key Positions	
Key Position	Key Rotation
N Normal	150°
X	140°
Y	130°
Z	120°



Dimensions in Inches (millimeters) are subject to change without notice.




Series 800 Mighty Mouse, UN Mating Thread PCB Mount Right Angle Header Receptacle 800-032 PCB Mounting Footprints


RIGHT ANGLE PCB FOOTPRINTS: SOCKET CONNECTORS SHOWN

Patterns shown are for component mounting side of PCB.


Contacts are .022 (0.56) max. diameter, mounting holes are 2-56 threaded inserts




5-3




6-1




6-4




6-6




6-7




7-1



7-10



8-2



8-13

Rev. 11/30/17

Dimensions in Inches (millimeters) are subject to change without notice.

© 2014 Glenair, Inc.

Series 80 Mighty Mouse

U.S. CAGE Code 06324

Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912
www.glenair.com C-20 E-Mail: sales@glenair.com

Rev. 06/05/19

Series 800 Mighty Mouse, UN Mating Thread PCB Mount Right Angle Header Receptacle 800-032 PCB Mounting Footprints




Series 800


RIGHT ANGLE PCB FOOTPRINTS: SOCKET CONNECTORS SHOWN

Patterns shown are for component mounting side of PCB.


Contacts are .022 (0.56) max. diameter, mounting holes are 2-56 threaded inserts




9-4




9-19




9-200



10-2



10-5



10-201

C