









RECOMMENDED PCB LAYOUT
FOR USE WITH 0.20 [.008] THICK STENCIL

6	7	—	30.48 [1.200]	1 4	32.61 [1.284]	30	6-147279-4
6	7	—	30.48 [1.200]	1 3	32.61 [1.284]	28	6-147279-3
6	7	—	30.48 [1.200]	1 0	32.61 [1.284]	22	6-147279-2
6	7	—	30.48 [1.200]	8	32.61 [1.284]	18	6-147279-1
9	7	44mm	30.48 [1.200]	1 2	32.61 [1.284]	26	6-147279-0
	7	44mm	17.78 [.700]	7	19.91 [.784]	16	5-147279-9
	7	24mm	12.7 [.500]	5	14.83 [.584]	12	5-147279-8
9	7	24mm	7.62 [.300]	3	9.75 [.384]	8	5-147279-7
	7	44mm	27.94 [1.100]	1 1	30.07 [1.184]	24	5-147279-6
	7	44mm	22.86 [.900]	9	24.99 [.984]	20	5-147279-5
8	7	24mm	2.54 [.100]	1	4.67 [.184]	4	5-147279-4
	7	32mm	15.24 [.600]	6	17.37 [.684]	14	5-147279-3
	7	24mm	10.16 [.400]	4	12.29 [.484]	10	5-147279-2
	7	24mm	5.08 [.200]	2	7.21 [.284]	6	5-147279-1
	7	24mm	5.08 [.200]	2	7.21 [.284]	6	1-147279-1
	3	44mm	30.48 [1.200]	1 2	32.61 [1.284]	26	1-147279-0
	3	44mm	17.78 [.700]	7	19.91 [.784]	16	147279-9
9	3	24mm	12.7 [.500]	5	14.83 [.584]	12	147279-8
9	3	24mm	7.62 [.300]	3	9.75 [.384]	8	147279-7
	3	44mm	27.94 [1.100]	1 1	30.07 [1.184]	24	147279-6
	3	44mm	22.86 [.900]	9	24.99 [.984]	20	147279-5
	3	24mm	2.54 [.100]	1	4.67 [.184]	4	147279-4
	3	32mm	15.24 [.600]	6	17.37 [.684]	14	147279-3
	3	24mm	10.16 [.400]	4	12.29 [.484]	10	147279-2
	3	24mm	5.08 [.200]	2	7.21 [.284]	6	147279-1
	PLATING	TAPE WIDTH	C	B	A	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER 10JUL00		 TE Connectivity						
DIMENSIONS: mm [INCHES]		CHK J. GESFORD 10JUL00								
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. GESFORD 10JUL00		NAME SURF. MT. HDR. ASSY, MOD II, B/W, VERT, D/R, .100 x .100 C/L, .025 SQ POST, W/ PICK AND PLACE CAP						
		PRODUCT SPEC —								
		APPLICATION SPEC —								
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.13 [.005] 4 PLC ± — ANGLES ± —		WEIGHT —		SIZE A2	CAGE CODE 00779	DRAWING NO C-147279	RESTRICTED TO —			
MATERIAL 		FINISH SEE TABLE		CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 1	REV R2