


FEATURES

T-3 1/4 Wedge Base - Non-Polarized
 Wide Input Voltage Range
 10 - 30V DC
 10 - 12V AC
 Low Power Usage
 Efficacy of 56Lm/Watt
 Viewing Angle 100°
 Color Temperature 3000°k
 CRI >80



TYPICAL ELECTRICAL & OPTICAL OPERATING CHARACTERISTICS

(Ta = 25 degree C)

JKL PART NUMBER	VOLTAGE DC			WATTS			LUMINOUS INTENSITY Lm
	MIN	NOM	MAX	MIN	NOM	MAX	
LE-WB2W-12W	10	12	30	1.75	2.2	2.5	130

JKL PART NUMBER: LE-WB2W-12W

			METRIC	DIMENSIONS ARE MILLIMETER/INCH	JKL COMPONENTS CORPORATION			
REV. NO.	DESCRIPTION/ECO NUMBER	APPV'D DATE	THIRD ANGLE PROJECTION	TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- REF. 2 PL +/- REF. ANGLE +/-	TITLE	SIZE	FSCM NO.	DRAWING NO.
D	FEAT. 10-24VAC TO 10-12VAC, CHART V TO DC	8/5/16	THIRD ANGLE PROJECTION	1 PL +/- REF. 2 PL +/- REF. ANGLE +/-	T-3 1/4 WEDGE BASE LED LAMP	A	55335	LE-WB2W-12W
C	CHANGE DIMS .79" TO .83" & 1.81" TO 1.85"	3/23/16						
B	ADD TO FEATURES AND CHANGE CHART	2/61/16						
A	CHANGE VIEWING ANGLE TO 100°	1/131/16						
	RELEASED	11/10/15						
			- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE	RELEASED DATE	REVISION DATE	REV. NO.
					NONE	11/10/15	8/5/16	D
								SHEET 1 OF 1