







Technical specification:

Technische Daten:

Dielectric withstanding voltage/ Spannungsfestigkeit:	1000 V, 50 Hz 1 min.
Current rating/ Strombelastbarkeit:	Signal contacts/ 7,5 A (UL) Signalkontakte: 5 A (CSA,VDE)
Insulation resistance/ Isolationswiderstand:	≥5 GΩ
Temperature range/ Temperaturbereich:	-55 °C ... +125 °C
Mating cycles/ Steckzyklen:	Quality class 3 = 50 Gütestufe 3

Materials/

Werkstoffe:

Contact/ Kontakt:	Cu alloy, Au over Ni
Insulator/ Isolierkörper:	PBT GF UL 94 V-0, green/grün
Shell/ Gehäuse:	Steel, Sn over Ni
Threaded spacer clip/ Abstandsbolzen:	Cu alloy, Sn over Ni
Collar/ Scheibe:	Cu alloy, Sn over Ni

Installation specifiation/

Montagedaten:

Maximum torque Value for thread/ empfohlenes Drehmoment für Gewinde:	6 in.LB/ 67 Ncm
PCB clip for hole diameter/ PCB Clip für Lochdurchmesser:	Ø3,1 mm
Circuit board thickness/ Leiterplattenstärke:	1,6 mm

Part no. / Part marked Art.-Nr. / Bedruckung:	Contact plating/ Kontakt Veredelung:
3017W2PAR99E20X	Signal Contact Signal Kontakt:
	Gold Flash over Nickel Gold über Nickel

Index: Original	Scale/Maßstab: 2:1		D-SUB Combination Male 17W2P with threaded rear spacer PCB clip D-SUB Combination Stiftleiste 17W2P mit Abstandsbolzen-Clip	dwg no / Z.-nr.: 13K1A5262	DIN-A3 1 / 1
Status: InBearbeitung					
RoHS & REACH compliant/ konform					