

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Winter Warden 08-Aug-22 CHK 15-Mar-17 Daniel Zhang Ricardo Robane		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 P/LC ±.1 1 P/LC ±0.2 2 P/LC ±0.2 3 P/LC ±0.2 4 P/LC ±0.2 ANGLES ±.1 FINISH		NAME DUOPLUG MARK II SIDE LOCKING - PRODUCT SPEC 108-18785-I APPLICATION SPEC 1114-18467-I	
		SIZE A1		CAGE CODE DRAWING NO 2306286	
MATERIAL - - -		WEIGHT - CUSTOMER DRAWING		RESTRICTED TO - SCALE 8:1 SHEET 1 OF 2 REV B2	

REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

GWEPT 750°C NO FLAME & UL94-V0, SILVER PLATED VERSION																		
-		X	X	X	X	X	X	X	X	9	20.0	24.9	23.5	20.0	3.75	2/3	1-2369990-9	
Red							X	X	X	4	7.5	12.4	11.0	7.5	6.25	3/4	1-2369990-4	
Color Code 	10	9	8	7	6	5	4	3	2	1	POS.	A	B	C	D	E		PN Bestell-Nr.
CAVITIES LOADED																		

PA GF, GWEPT 750°C NO FLAME & UL94-V0, TIN PLATED VERSION																		
-	X	0	X	X	0	X	0	X	0	X	10	22.5	27.4	26	22.5	6.25	3/4	1-2306287-0
-	X	X	X	X	X	X	X	X	X	X						3.75	2/3	1-2306286-0
-		X	X	X	X	X	X	X	X	X	9	20	24.9	23.5	20	3.75	2/3	1-2306286-9
Black		X	X	X	X	X	X	X	X	X							2/3	2306286-9
-		X	0	X	0	X	0	X	0	X							2/3	3-2306287-9
-		X	0	X	X	0	X	0	X	X							2/3	2-2306287-9
-		X	X	0	X	0	X	0	X	X						-	-	1-2306287-9
Green		X	0	X	X	0	X	0	X	X						3.75	2/3	2306287-9
			X	0	X	0	X	X	X	X	8	17.5	22.4	21	17.5	3.75	2/3	2306287-8
-			X	X	X	X	X	X	X	X						11.25	5/6	1-2306286-8
-			X	X	X	X	X	X	X	X						3.75	2/3	2306286-8
				X	0	X	0	X	0	X	7	15	19.9	18.5	15	11.25	5/6	3-2306287-7
Black				X	0	X	0	X	0	X						8.75	4/5	2-2306287-7
-				X	0	X	0	X	0	X						3.75	2/3	1-2306287-7
Blue				X	0	X	0	X	0	X						3.75	2/3	2306287-7
				X	X	X	X	X	X	X						11.25	5/6	2-2306286-7
-				X	X	X	X	X	X	X						3.75	2/3	1-2306286-7
Black				X	X	X	X	X	X	X						2/3	2306286-7	
-					X	X	X	X	X	X	6	12.5	17.4	16	12.5	8.75	4/5	2-2306286-6
-					X	X	X	X	X	X						3.75	2/3	1-2306286-6
-					X	X	X	X	X	X						1.25	1/2	2306286-6
-					X	0	X	X	0	X						3.75	2/3	4-2306287-6
-					X	X	0	X	0	X						8.75	4/5	3-2306287-6
-					X	0	X	X	0	X						4/5	2-2306287-6	
-					X	0	X	X	0	X						3.75	2/3	1-2306287-6
Black					X	0	X	X	0	X						3.75	2/3	2306287-6
-						X	0	X	0	X	5	10	14.9	13.5	10	3.75	2/3	2-2306287-5
-						X	X	X	0	X						6.25	3/4	1-2306287-5
Blue						X	X	X	0	X						6.25	3/4	2306287-5
-						X	X	X	X	X						1.25	1/2	5-2306286-5
-						X	X	X	X	X						6.25	3/4	4-2306286-5
-						X	X	X	X	X						3.75	2/3	3-2306286-5
Green						X	X	X	X	X						1.25	1/2	2-2306286-5
Red						X	X	X	X	X						6.25	3/4	1-2306286-5
Black						X	X	X	X	X						3.75	2/3	2306286-5
-							X	X	X	X	4	7.5	12.4	11	7.5	6.25	3/4	3-2306286-4
-							X	X	X	X						1.25	1/2	2-2306286-4
Red							X	X	X	X						6.25	3/4	1-2306286-4
Black							X	X	X	X						1.25	1/2	2306286-4
-								X	0	X	3	5	9.9	8.5	5	1.25	1/2	3-2306287-3
-								X	0	X						3.75	2/3	2-2306287-3
Green								X	0	X						1.25	1/2	1-2306287-3
Blue								X	0	X						3.75	2/3	2306287-3
-								X	X	X						3.75	2/3	3-2306286-3
-								X	X	X						1.25	1/2	2-2306286-3
Black								X	X	X						3.75	2/3	1-2306286-3
Red								X	X	X						1.25	1/2	2306286-3
Color Code	10	9	8	7	6	5	4	3	2	1	POS.	A	B	C	D	E		PN Bestell-Nr.
	CAVITIES LOADED																	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

Winter Wang

08-Aug-22

CHK

Daniel Zhang

15-Mar-17

DIMENSIONS:

mm

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

FINISH

±

±0.2

±0.2

±0.2

±0.2

±

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

108-18785-1

114-18467-1

PRODUCT SPEC

APPLICATION SPEC

MATERIAL

-

-

DWN

Winter Wang

08-Aug-22

CHK

Daniel Zhang

15-Mar-17

APVD

Riccardo Robore

15-Mar-17

NAME

DUOPLUG MARK II SIDE LOCKING

-

SIZE

A 1

CAGE CODE

C=2306286

DRAWING NO

-

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE

8:1

SHEET

2

OF

2

REV

B 21