





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		E2	REVISED PER ECR-10-013696	19AUG10	HMR	GJ

1. SPECIFICATIONS:
MAGNET WIRE #18 - #34 AWG, 1.02MM(.040)
-0.16MM(.006) DIA. COPPER.
2. POCKET RECOMMENDATION: #1601427
3. TERMINAL TO BE APPLIED PER TYCO ELECTRONICS
SPECIFICATION #114-13166 FIGURE 15.
4. SELECTIVE PLATE THIS AREA:
0.00076 [.00030] MIN GOLD PLATE OVER
0.00127 [.00050] MIN NICKEL UNDERPLATE
OVER ENTIRE TERMINAL.
5. PRELIMINARY - NOT FOR PRODUCTION.
6. TWO(2) TERMINALS SHOWN FOR ILLUSTRATION
PURPOSES ONLY.



-	-	-
4	-	5 2-1601018-3
PRE-TIN PLATE OVER COPPER UNDERPLATE	131-042-014	2-1601018-2
4	-	5 1601018-3
PRE-TIN PLATE OVER COPPER UNDERPLATE	131-044-014	1601018-2
UNPLATED	-	5 1601018-1
FINISH	REFERENCE PART NUMBER	TE PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS: mm [INCHES]	DWN J.WELLER 11JAN2002	Tyco Electronics Corporation Harrisburg, PA 17105-3608
	CHK M.FEHER 11JAN2002	
	APVD K.RANDOLPH 11JAN2002	NAME STANDARD RANGE WIRE TO 4.75[.187] BARB TAB SIAMEZE TERMINAL
	PRODUCT SPEC 108-2085	
MATERIAL BRASS, FULL HARD	APPLICATION SPEC 3	SIZE A2
	FINISH SEE TABLE	
WEIGHT -		CAGE CODE 00779
CUSTOMER DRAWING		DRAWING NO C=1601018
SCALE 9:1		RESTRICTED TO -
SHEET 1 of 1		REV E2