


B



1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. PART NUMBERS:
 - A. SEE SHEET 2 FOR METHOD A.
 - B. SEE SHEET 3 FOR MODIFIED METHOD A, PAIR FLIPPED.
4. METHOD A CASSETTES COMPLY WITH ANSI/TIA-568-C.O. SEE ANSI/TIA-568-C.O FOR POLARITY DETAILS AND EXAMPLE OF A BASIC LINK.
5. MATERIALS:
 - A. BOX AND LID: PLASTIC
 - B. ADAPTER: COMPOSITE PLASTIC
6. CASSETTE WEIGHT: 3.53oz [100g]
7. DIMENSIONS IN BRACKETS ARE METRIC.



- SEE SHEETS 2 AND 3
FOR ARTWORK DETAILS

☐

SHOWN W/O DUSTCAPS


1

2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

12 FIBER DUPLEX LC CASSETTE - METHOD A	
PART NUMBER	DESCRIPTION
FC2ZO-12-10AS	12 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-12-10AS	12 FIBER 50/125um OM4
FC2XO-12-10AS	12 FIBER 50/125um OM3 OPTIMIZED
FC2XN-12-10AS	12 FIBER 50/125um OM3
FC25N-12-10AS	12 FIBER 50/125um OM2
FC26N-12-10AS	12 FIBER 62.5/125um OM1
FC29N-12-10AS	12 FIBER 9/125um OS1/OS2
FC2SA-12-10AS	12 FIBER 50/125um OM4+, SIGNATURE CORE



METHOD A - FIBER LAYOUT

							TITLE 12 FIBER DUPLEX LC CASSETTE METHOD A CUSTOMER DRAWING					
							ITEM REVISION NAME 10F113AD/00			PANDUIT TM		
							DATASET FILE NAME 10F113AD_DC/00A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .03 [.8] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °  THIRD ANGLE PROJECTION			MATERIAL: SEE NOTES SHEET 1		
R	10-10-12	SAT	TMSE		RELEASED TO PRODUCTION	10F113AD-DC				DRAWING NUMBER: 10F113AD-DC		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 10-01-12	CHK TMSE	SCALE NONE	SHT 2 OF 3	SIZE A

2


1

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

12 FIBER DUPLEX LC CASSETTE - MODIFIED METHOD A, PAIR FLIPPED	
PART NUMBER	DESCRIPTION
FC2ZO-12-10AF	12 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-12-10AF	12 FIBER 50/125um OM4
FC2XO-12-10AF	12 FIBER 50/125um 10 GbE OM3 OPTIMIZED
FC2XN-12-10AF	12 FIBER 50/125um 10 GbE OM3
FC25N-12-10AF	12 FIBER 50/125um OM2
FC26N-12-10AF	12 FIBER 62.5/125um OM1
FC29N-12-10AF	12 FIBER 9/125um OS1
FC2SA-12-10AF	12 FIBER 50/125um OM4+, SIGNATURE CORE



MODIFIED METHOD A, PAIR FLIPPED - FIBER LAYOUT

						TITLE 12 FIBER DUPLEX LC CASSETTE MODIFIED METHOD A, PAIR FLIPPED			
						CUSTOMER DRAWING			
						ITEM REVISION NAME 10F113AD/00	PANDUIT TM		
						DATASET FILE NAME 10F113AD_DC/00A			
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x : .03 (.8) .xxx : .005 (.127) .xx : .01 (.25) ANGLES : 5 °			MATERIAL : SEE NOTES SHEET 1
						THIRD ANGLE PROJECTION			DRAWING NUMBER: 10F113AD-DC
						DRAWN BY SAT	DATE 10-01-12	CHK TMSE	SCALE NONE
									SHT 3 OF 3
									A
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN			
R	10-10-12	SAT	TMSE		RELEASED TO PRODUCTION	10F113AD-DC			

2

1