








NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; BLACK
- CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
- PLASTIC BRACKETS: PBT GF UL 94 V-0; BLACK
- THREADED LOCKS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- FIXING-PLATE: PBT GF UL 94 V-0; BLACK
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: **163A19149X CONEC ABC**

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale:	2:1 (5:1)	
							material:	see notes	
							title: D-SUB MALE 90° 25pos. SOLDER PIN ANGLED 0.590inch threaded lock, plastic bracket fixing plate		
DO NOT ALTER CAD DRAWING BY HAND					date	name	dwg no: 16K1A2738 part no: 163A19149X		
				drawn	02.12.10	Schmidt			
				appd.	08.12.10	Fischer			
				norm		DIN-A3 sh: 1			
				d-old					
a				Origin					
rev.	description	date	name						

