




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00		J	EC 0G3C 0759 04	02FEB05	BSV JLG
			J1	REVISED PER ECO-09-020689	02SEP09	KK AEG

- 1
- CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS
- 2
- USE WITH #26-#30 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS
- 3
- THE DIMENSION APPLIES WITH THE FORWARD PRELOAD STOP IN CONTACT WITH THE HOUSING SURFACE
- 4
- POINT OF MEASUREMENT FOR PLATING THICKNESS
- 5
- FOR INDIVIDUAL ASSEMBLIES SEE PART NUMBER 103650
- 6
- ASSEMBLIES ARE JOINED BY THE CARRIER STRIP. ORDER QUANTITY REFLECTS TOTAL NUMBER OF INDIVIDUAL ASSEMBLIES REQUIRED. SEE TABLE FOR NUMBER OF ASSEMBLIES PER STRIP.
- 7
- POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS)
- 8
- MAXIMUM ALLOWABLE BOW OF ASSEMBLY NOT TO EXCEED.055.
- 9
- CONTACTS: .000100-.000200 BRIGHT TIN-LEAD OVER .000050 NICKEL
- 10
- CONTACTS: .000100-.000200 MATTE TIN OVER .000050 NICKEL
- 11
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

			2	2.40	1.198	1-103648-1	12	6-103976-1
			2	2.20	1.098	1-103648-0	1 1	6-103976-0
	OBSOLETE		2	2.00	.998	103648-9	10	5-103971-9
	OBSOLETE		2	1.80	.898	103648-8	9	5-103971-8
			2	1.60	.798	103648-7	8	5-103971-7
	OBSOLETE		2	1.40	.698	103648-6	7	5-103971-6
	OBSOLETE		4	2.39	.598	103648-5	6	5-103971-5
			4	1.99	.498	103648-4	5	5-103971-4
			5	1.99	.398	103648-3	4	5-103971-3
			8	2.40	.298	103648-2	3	5-103971-2
			10	2.00	.198	103648-1	2	5-103971-1
	OBSOLETE		2	2.40	1.198	1-103648-1	12	1-103971-1
	OBSOLETE		2	2.20	1.098	1-103648-0	1 1	1-103971-0
	OBSOLETE		2	2.00	.998	103648-9	10	103971-9
	OBSOLETE		2	1.80	.898	103648-8	9	103971-8
	SUPERSEDED		2	1.60	.798	103648-7	8	103971-7
	OBSOLETE		2	1.40	.698	103648-6	7	103971-6
	OBSOLETE		4	2.39	.598	103648-5	6	103971-5
			4	1.99	.498	103648-4	5	103971-4
			5	1.99	.398	103648-3	4	103971-3
			8	2.40	.298	103648-2	3	103971-2
			10	2.00	.198	103648-1	2	103971-1
		PLATING		B	A	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER ON STRIP