

440-144

Composite Ultra Low Profile EMI/RFI Micro-Banding Backshell with Shrink Boot Porch and Self-Locking Rotatable Coupling

CONNECTOR DESIGNATOR:

F MIL-DTL-38999 Series I, II
H MIL-DTL-38999 Series III and IV

SELF-LOCKING

ROTATABLE COUPLING

ULTRA LOW PROFILE

Angle and Profile

S - Straight **A** - 90° Low Profile, Std
T - 45° Elbow **E** - 90° Low Profile, Split
W - 90° Low Profile, Solid

Cable Entry

(See Table II)
 Omit for E and
 W Option Only

Drain Hole Option

(Omit "D" if not required)

Shrink Boot Option

Shrink boot supplied
 with **T** option
 O-Ring will not be supplied
 with Connector Designator A
 (Omit for none)

Product Series

440 - EMI/RFI Non-Environmental
 Micro-Banding Backshells

Basic Part
Number

144

Finish Symbol

(See Table III)

440

H

S

144

XM

15

09

D

B

T

S

Connector Designator

A, F or H
 (See Table I)
 See Note 1

Connector Shell Size








(See Table I)
 See Note 1

Band Option

B - 600-057
K - 600-057-1
 (Omit for none)

Shield
Termination
Slot

(Omit for none)



440-144
Composite Ultra Low Profile EMI/RFI
Micro-Banding Backshell with Shrink Boot Porch
and Self-Locking Rotatable Coupling



TABLE I: SHELL SIZE

Shell Size		Entry Code Available for Straight, 45° and 90° Std Configuration	G Max	H ± .03	J	K	L ± .09	M ± .09	N Max	P Max
A & F	H									
08	09	04	.630 (16.0)	1.042 (26.5)	.304 (7.7)	.160 (4.1)	.690 (17.5)	.880 (22.4)	1.360 (34.5)	.810 (20.6)
10	11	05	.660 (16.8)	1.107 (28.1)	.432 (11.0)	.174 (4.4)	.750 (19.1)	1.000 (24.5)	1.420 (36.1)	.810 (20.6)
12	13	07	.720 (18.3)	1.174 (29.8)	.546 (13.9)	.195 (5.0)	.810 (20.6)	1.130 (28.7)	1.480 (37.6)	.820 (20.8)
14	15	09	.830 (21.1)	1.241 (31.5)	.670 (17.0)	.315 (8.0)	.880 (22.4)	1.310 (33.3)	1.550 (39.4)	.880 (22.4)
16	17	05 and 11	.910 (23.1)	1.305 (33.1)	.796 (20.2)	.385 (9.8)	.940 (23.9)	1.380 (35.1)	1.610 (40.9)	.930 (23.6)
18	19	07 and 13	.930 (23.6)	1.371 (34.8)	.902 (22.9)	.445 (11.3)	.970 (24.6)	1.440 (36.6)	1.640 (41.7)	.990 (25.1)
20	21	09 and 15	1.040 (26.4)	1.438 (36.5)	1.027 (26.1)	.525 (13.3)	1.060 (26.9)	1.630 (41.4)	1.730 (43.9)	1.060 (26.9)
22	23	11 and 16	1.120 (28.4)	1.505 (38.2)	1.152 (29.3)	.595 (15.1)	1.130 (28.7)	1.750 (44.5)	1.800 (45.7)	1.130 (28.7)
24	25	07, 13 and 17	1.180 (30.0)	1.572 (39.9)	1.276 (32.4)	.655 (16.6)	1.190 (30.2)	1.880 (47.8)	1.860 (47.2)	1.050 (26.7)
24*	25		1.020 (26.0)	1.850 (47.0)	1.460 (37.1)	.450 (11.4)				1.050 (26.7)

*See Note 2

TABLE II: CABLE ENTRY

Entry Code	D ± .030	E ± .060	F ± .090
04	.250 (6.4)	.720 (18.3)	.870 (22.1)
05	.310 (7.9)	.750 (19.1)	.930 (23.6)
07	.440 (11.2)	.750 (19.1)	1.000 (25.4)
09	.560 (14.2)	.760 (19.3)	1.030 (26.2)
11	.680 (17.3)	.780 (19.8)	1.050 (26.7)
13	.810 (20.6)	.790 (20.1)	1.060 (26.9)
15	.940 (23.9)	.820 (20.8)	1.090 (27.7)
16	1.000 (25.4)	.860 (21.8)	1.130 (28.7)
17	1.160 (29.5)	.890 (22.6)	1.160 (29.5)

TABLE III: FINISH

Symbol	Finish Description
XM	2000 Hour Corrosion Resistant Electroless Nickel
XMT	2000 Hour Corrosion Resistant Ni-PTFE, Nickel-Fluorocarbon Polymer. <i>1000 Hour Grey™</i>
XW	2000 Hour Corrosion Resistant Cadmium/Olive Drab over Electroless Nickel

NOTES

1. 770-001S**-0 shrink boot supplied with T option. See shrink boot product page for more details.
2. For Sym "E" low profile split shell sizes 24 and 25 dimensions, use indicator row in Table I.
3. Coupling nut supplied unplated.
4. See Table I in Intro for front-end dimensional details.