





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		E6	REVISED PER ECR-14-015111	10OCT2014	GRZ	JL

- SPECIFICATIONS:
MAGNET WIRE #18 - #34 AWG,
1.02 [.040] - 0.16 [.006] DIA COPPER.
- POCKET RECOMMENDATION: #1601425
- TERMINAL APPLICATION TO COMPLY WITH TYCO
ELECTRONICS SPECIFICATION 114-13166 FIG 6.
- NOTES:
TERMINALS SUPPLIED ON REELS, CAN BE
SUPPLIED LOOSE PIECE,
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER
D.RENAUD/D.SINISI
- NON-STANDARD PACKAGING. ALL PLASTIC REEL AND PLASTIC
INTERLEAVING. PLACED IN A PLASTIC BAG.
- SELECTIVE PLATE AREA 0.0019 [.000075] MIN THICK SILVER.
ENTIRE TERMINAL IS UNDERPLATED WITH NICKEL.
- PRELIMINARY - NOT FOR PRODUCTION.



STANDARD	7	-	1601072-5
STANDARD	7	-	8 3-1601072-5
6	PRE-TIN PLATE OVER COPPER UNDERPLATE	-	8 3-1601072-4
STANDARD	PRE-TIN PLATE OVER COPPER UNDERPLATE	-	3-1601072-2
STANDARD	PRE-TIN PLATE OVER COPPER UNDERPLATE	131-140-014	2-1601072-2
STANDARD	PRE-TIN PLATE OVER COPPER UNDERPLATE	131-139-014	1601072-2
PACKAGING	FINISH	REFERENCE PART NUMBER	TE PART NUMBER

5
OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.WELLER 11JAN2002	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK M.FEHER 11JAN2002		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K.RANDOLPH 11JAN2002	NAME STD. WIRE RANGE TO .187 X .020 MULTI-BARB TAB SIAMEZE TERMINAL	
0 PLC ± - 1 PLC ± 0.25 [.010] 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± 2°		PRODUCT SPEC 108-2085 APPLICATION SPEC 3		
MATERIAL BRASS, FULL HARD		WEIGHT -	SIZE A2	CAGE CODE 00779
FINISH SEE TABLE		CUSTOMER DRAWING	DRAWING NO C=1601072	RESTRICTED TO -
		SCALE 6:1	SHEET 1 OF 1	REV E6