

RTF Series


7.2mm x 7.2mm Low Profile Rotary DIP Switches

Features/Benefits

- New generation
- Most compact rotary DIP switch
- Thru-hole, Crimped, J-Bend, Angled and Surface Mount Models
- New designs with different actuators
- IP67
- RoHS compatible and compliant

Typical Applications

- Industrial and control automation
- Automotive
- Computer and peripherals
- Instrumentation
- Security devices



H

DIP

Specifications

CONTACT RATING: 100mA, DC 5V (switching)
100mA, DC 50V (non-switching)

MECHANICAL & ELECTRICAL LIFE: 10,000 cycles

INITIAL CONTACT RESISTANCE: 100 milliohms max.

INSULATION RESISTANCE: 100 megohms min.

OPERATING TEMPERATURE: -40°C to 85°C.

STORAGE TEMPERATURE: -40°C to 85°C.

OPERATING FORCE: 200 gf max.

SOLDER CONDITIONS:

- Iron soldering: C/K/S/A/J termination: 3s/350°C
- Wave soldering: C/K/A termination: 5s/280°C
- Reflow soldering: S/J termination: 10s/260°C

SOLDERABILITY: Dip and look solderability testing per C&K spec #448

PACKAGING: Switches are supplied in rigid dispensing tubes in full-tube quantities only, this may affect order quantities. Number of switches per tube varies with model. Tape and reel packing is only available with "S" and "J" type terminations.

Materials

COVER: Stainless steel

BASE: LCP

ACTUATOR: LCP

CONTACTS: Phosphor bronze, gold plated

SPRING & GUIDE PLATE: Stainless steel

TERMINALS: Brass, gold plated

O-RING: Silicon

How To Order

The Build-A Switch concept allows you to mix and match options to create the switch you need. Below is a complete listing of options shown in catalog. To order, simply select desired option from each category and place in the appropriate box.

RTF							
Number of positions							
04	4 position						
10	10 position						
16	16 position						
Coding							
R	Real code						
C	Complement code						
Actuator							
0	Arrow (Height = 0 mm)						
1	Slotted Spindle (Height = 3 mm)						
2	Cross (Height = 0 mm)						
3	Arrow (Height = 3 mm)						
Terminations							
C	Thru-hole (Ter' 3 x 3)						
K	Crimped (Ter' 3 x 3)						
S	SMD Gull Wing						
A	Angled Type						
J	'J' Bend						
Packaging							
(None)	Tube						
R	Tape & Reel (only available for termination type S and J)						



Third Angle
Projection

RTF Series

7.2mm x 7.2mm Low Profile Rotary DIP Switches

CODING

R Real Code

04 POSITION

		Real Code				
		C	1	2	4	8
04 POSITION	0					
	1					
	2					
	3					

10 POSITION

		Real Code				
		C	1	2	4	8
10 POSITION	0					
	1					
	2					
	3					
	4					
	5					
	6					
	7					
	8					
	9					

16 POSITION

		Real Code				
		C	1	2	4	8
16 POSITION	0					
	1					
	2					
	3					
	4					
	5					
	6					
	7					
	8					
	9					
	A					
	B					
	C					
	D					
	E					
	F					

C Complement Code

04 POSITION

		Complement Code				
		C	1	2	4	8
04 POSITION	0	●	●	●	●	●
	1	●		●	●	●
	2	●	●		●	●
	3				●	●

10 POSITION


		Complement Code				
		C	1	2	4	8
10 POSITION	0					
	1					
	2					
	3					
	4					
	5					
	6					
	7					
	8					
	9					

16 POSITION


		Complement Code				
		C	1	2	4	8
16 POSITION	0					
	1					
	2					
	3					
	4					
	5					
	6					
	7					
	8					
	9					
	A					
	B					
	C					
	D					
	E					
	F					

ACTUATOR


0 Arrow (Height = 0 mm)





1 Slotted Spindle (Height = 3 mm)



2 Cross (Height = 0 mm)



3 Arrow (Height = 3 mm)




Third Angle
Projection


RTF Series 7.2mm x 7.2mm Low Profile Rotary DIP Switches

TERMINATIONS


C Thru-hole




K Crimped (Ter' 3 x 3)




S SMD Gull Wing



J Bend SMD



A Angled Type



Dimensions are shown: Inch (mm)
Specifications and dimensions subject to change

RTF Series

7.2mm x 7.2mm Low Profile Rotary DIP Switches


TAPE & REEL





H

DIP

The tape and reel is applicable for
Actuator 0 or 2 with
Termination S or J
1300 pcs/reel



The tape and reel is applicable for
Actuator 1 or 3 with
Termination S or J
800 pcs/reel



Third Angle
Projection

Dimensions are shown: Inch (mm)
Specifications and dimensions subject to change