





9	OBSOLETE	9.51	19.02	7.6	15.2	19.35	7.795	15.2	17.34	2	7	8	40	6-1375870-8
9	OBSOLETE	9.11	18.22	7.2	14.4	18.55	7.395	14.4	16.54				38	6-1375870-7
9	OBSOLETE	8.71	17.42	6.8	13.6	17.75	6.995	13.6	15.74				36	6-1375870-6
9	OBSOLETE	8.31	16.62	6.4	12.8	16.95	6.595	12.8	14.94				34	6-1375870-5
		7.91	15.82	6	12	16.15	6.195	12	14.14				32	6-1375870-4
9	OBSOLETE	7.51	15.02	5.6	11.2	15.35	5.795	11.2	13.34				30	6-1375870-3
9	OBSOLETE	7.11	14.22	5.2	10.4	14.55	5.395	10.4	12.54				28	6-1375870-2
9	OBSOLETE	6.71	13.42	4.8	9.6	13.75	4.995	9.6	11.74				26	6-1375870-1
		6.31	12.62	4.4	8.8	12.95	4.595	8.8	10.94				24	6-1375870-0
9	OBSOLETE	5.91	11.82	4	8	12.15	4.195	8	10.14	2	7	8	22	5-1375870-9
9	OBSOLETE	5.51	11.02	3.6	7.2	11.35	3.795	7.2	9.34				20	5-1375870-8
9	OBSOLETE	5.11	10.22	3.2	6.4	10.55	3.395	6.4	8.54				18	5-1375870-7
		4.71	9.42	2.8	5.6	9.75	2.995	5.6	7.74				16	5-1375870-6
		4.31	8.62	2.4	4.8	8.95	2.595	4.8	6.94				14	5-1375870-5
		3.91	7.82	2	4	8.15	2.195	4	6.14				12	5-1375870-4
		3.51	7.02	1.6	3.2	7.35	1.795	3.2	5.34				10	5-1375870-3
9	OBSOLETE	3.11	6.22	1.2	2.4	6.55	1.395	2.4	4.54				8	5-1375870-2
		2.71	5.42	0.8	1.6	5.75	0.995	1.6	3.74				6	5-1375870-1
		9.51	19.02	7.6	15.2	19.35	7.795	15.2	17.34				40	1-1375870-8
9	OBSOLETE	9.11	18.22	7.2	14.4	18.55	7.395	14.4	16.54				38	1-1375870-7
9	OBSOLETE	8.71	17.42	6.8	13.6	17.75	6.995	13.6	15.74				36	1-1375870-6
9	OBSOLETE	8.31	16.62	6.4	12.8	16.95	6.595	12.8	14.94				34	1-1375870-5
		7.91	15.82	6	12	16.15	6.195	12	14.14				32	1-1375870-4
9	OBSOLETE	7.51	15.02	5.6	11.2	15.35	5.795	11.2	13.34				30	1-1375870-3
9	OBSOLETE	7.11	14.22	5.2	10.4	14.55	5.395	10.4	12.54				28	1-1375870-2
9	OBSOLETE	6.71	13.42	4.8	9.6	13.75	4.995	9.6	11.74				26	1-1375870-1
		6.31	12.62	4.4	8.8	12.95	4.595	8.8	10.94				24	1-1375870-0
9	OBSOLETE	5.91	11.82	4	8	12.15	4.195	8	10.14	2	3		22	1375870-9
		5.51	11.02	3.6	7.2	11.35	3.795	7.2	9.34			20	1375870-8	
		5.11	10.22	3.2	6.4	10.55	3.395	6.4	8.54			18	1375870-7	
		4.71	9.42	2.8	5.6	9.75	2.995	5.6	7.74			16	1375870-6	
		4.31	8.62	2.4	4.8	8.95	2.595	4.8	6.94				14	1375870-5
		3.91	7.82	2	4	8.15	2.195	4	6.14				12	1375870-4
		3.51	7.02	1.6	3.2	7.35	1.795	3.2	5.34				10	1375870-3
		3.11	6.22	1.2	2.4	6.55	1.395	2.4	4.54				8	1375870-2
		2.71	5.42	0.8	1.6	5.75	0.995	1.6	3.74				6	1375870-1
		DIM S	DIM T	DIM U	DIM V	W REF	DIM X	DIM Y	Z	FINISH			NO. OF POS. N	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. NO. TE_KOEGEL 01JUN2000 CHK. BY W. DAVIS 07JUN2000 APP'D. -		 TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm	0 P L/C ± 1 P L/C ± 2 P L/C ± 3 P L/C ± ANGLES ± FINISH	PRODUCT SPEC 108-1955 APPLICATION SPEC 114-13051 WEIGHT	AMPMODU MICRO INTERCONNECT RECEPTACLE ASSEMBLY -		
MATERIAL	 SEE TABLE	CUSTOMER DRAWING	SIZE CAGE CODE DRAWING NO A100779C-1375870	RESTRICTED TO	
			SCALE 20:	SHEET 1	OF 1 REV B2