


PRODUCT NUMBER

10141568-0001LF

1 | 2




3 |

4




## NOTE:

- CURRENT RATING: 3A AC/DC.
- WITHSTANDING VOLTAGE: 600V AC/MINUTE.
- TEMPERATURE RANGE: -40~120°C.
- INSULATION RESISTANCE: >=5000MΩ.
- CONTACT RESISTANCE: <=20mΩ.
- PLASTIC MATERIAL: PA6T, UL94V-0.
- TERMINAL MATERIAL: BRASS
- FINISH: GOLD FLASH





RECOMMENDED P.C.B LAYOUT  
ALL TOLERANCE ARE: ±0.05

mat'l. code				surface		tolerance	projection	product family
ltr	ecn	no	dr	date	tolerances unless otherwise specified			MINITEK
					angles	16<L ± 0.40		
					0°±5°	4<L<=16 ± 0.30	mm	
					L<=4	± 0.20	scale N.T.S.	
					dr	TONY LENG	2017-12-12	title
					engr	TONY LENG	2017-12-12	2.54mm SHROUDED HEADER
					chr	ZK HU	2017-12-12	VERTICAL, 30 POS.
					appd	TIM YAO	2017-12-12	
Amphenol FCi					dwg no	sheet 1 of 2	size	
						10141568	A4	
					type	Product Customer Drawing		
sheet	revision	A	A					
index	sheet	1	2					




## NOTES:

1. Reel[ $\phi 330 * 77\text{mm}$ ]
2. 200pcs/R,4R/Carton,800pcs/Carton
3. Heat-sealing cover tape
4. Black carrier
5. Big Plastic Bag(1000\*1000mm)
6. Carton(340\*340\*325mm,Thickness=5mm)
7. In each Big Plastic bag put two desiccants



CARRIER TAPE PACKING LENGTH  
END CONNECTORS LEADER (START)



mat'l. code				surface		tolerance	projection	product family
ltr	ecn	no	dr	date	tolerances unless otherwise specified			MINITEK
					angles	$16 < L \leq 0.40$		
					linear	$4 < L \leq 16 \pm 0.30$		
					$0^\circ \pm 5^\circ$	$L \leq 4 \pm 0.20$		
					dr	TONY LENG	2017-12-12	
					engr	TONY LENG	2017-12-12	
					chr	ZK HU	2017-12-12	
					appd	TIM YAO	2017-12-12	
sheet	revision	A	A					
index	sheet	1	2					