







LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DS	-		E	REVISED PER ECR-18-018075	19NOV2018	BH	E.W
			F	REVISED PER ECR-19-005609	23MAY2019	BH	E.W
			F1	REVISED PER ECR-19-008330	24MAY2019	BH	E.W
			F2	REVISED PER ECR-19-013181	22AUG2019	BH	E.W




SCALE 1:2



13.0 ^{+0.5} _{-0.1}	72.1±0.25	Ø 6.2±0.1	BLACK	1743067-3
13.0 ^{+0.5} _{-0.1}	72.1±0.25	Ø 5.0±0.1	BLACK	1743067-2
"Z"	"Y"	"X"	COLOR	P/N

NOTES.
1.GENERAL TOLERANCE : ±0.5
2.APPLICABLE CONTACT P/N : 521843-1
3.CAVITY MARK SHALL BE LOCATED APPROX. AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BH CHO	 TE Connectivity		
		CHK -			
DIMENSIONS: mm		APVD BW KANG	NAME TERMINAL BLOCK FOR DRYER		
		PRODUCT SPEC 108-61063			
		APPLICATION SPEC -	SIZE A300779		
MATERIAL PHENOLIC UL94 V-0		WEIGHT -	CAGE CODE C-1743067		
		CUSTOMER DRAWING	DRAWING NO 1743067		
			RESTRICTED TO		
			SCALE 1:1 SHEET 1 OF 1 REV F2		