



深圳市兴华鑫电子科技有限公司

Shenzhen xinghuaxin Electronic Technology Co., Ltd

承認書

SPECIFICATION FOR APPROVAL

客戶 (Customer):

客戶料號 (Customer P/N):

興華鑫型號 (Supplier P/N):

XHxDZ-2308-8 Ω 1W

產品名稱 (Description):

喇叭 (Speaker)

產品規格 (Specification):

指纹锁喇叭

客戶承認欄 (Customer Authorization Signature)	深圳市興華鑫電子科技有限公司 承認欄 (Supplier Audit)		
	審核	檢查	制作
	唐国兴	唐玉来	吴银娟
日期: 2022 年 04 月 19 日			
版次: A			

声音让生活更精彩!

地址: 深圳市宝安区新安街道新乐社区新乐路 88 号厂房四层

TEL: 0755-27892904

E-mail: jacky.tang@jsxhxdz.com

Http: www.jsxhxdz.com

深圳市兴华鑫电子科技有限公司

产品规格内容

1.Part Number: XHXDZ-2308-8 Ω 1W

2.Type: Dynamic Receiver / Speaker

3.Dimension:

$\varnothing$ 23mm $\times$ 7.8H

4.Weight: 7.5g

5. Electrical And Acoustical Characteristics (at 20℃)

5.1. Speaker Part:

5.1.1 Sound Pressure Level : 88 $\pm$ 3dB SPL

5.1.2 Rated Power Input:

Nominal Power : 0.5 W

Maximum Power : 1.0W

5.1.3 Rated Impedance : 8 $\pm$ 15% Ω

5.1.4 Resonance Frequency : 2000 $\pm$ 20%Hz (at 2.0V)

5.1.5 Test method :

The Speaker shall be mounted in a baffle described in the Fig.1,and tested with 2V(0.1W);
The measuring microphone shall be placed 10cm from the speaker in an anechoic chamber.

深圳市兴华鑫电子科技有限公司

产品规格内容

5.1.6.Block Diagram For Measurement Method.




FIG.1 (Speaker Measurement Method)

5.1.7.Frequency Response :

The swept sine-wave frequency response of a loudspeaker should ideally not deviate more than indicated per Fig.2

At 0.1m 0.1W

FIG..2(Loud speaker Typical Frequency Response)



深圳市兴华鑫电子科技有限公司

产品规格内容

6. MECHANICAL DRAWING

