

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		1	PROPOSED	—	—	—

- 1
- CONTINUOUS STRIP ON REELS WITH TERMINALS
LOCATED ON 6.86±0.08 [.270±.003] CENTERS
- 2
- SLOT ACCEPTS 0.57–0.81mm [#23–#20] AWG COPPER
MAGNET WIRE. TWO WIRES OF THE SAME SIZE MAX PER SLOT
FOR #23 GAGE. ONE WIRE MAX PER SLOT FOR #22–#20 AWG
- 3
- IDENTIFICATION NUMBER 15 FOR THE MAGNET WIRE SLOT SIZE.
- 4
- 0.25 [.010] MAX CARRIER CUT-OFF
- 5
- PRELIMINARY – NOT FOR PRODUCTION



0.002032 [.000080] MIN TIN PLATE		082 PRE-MILLED BRASS		5 1742860-1	
FINISH		MATERIAL		PART NO.	
D DOCUMENT.		DWN 27OCT10 JR RUTH		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
CHK 27OCT10 KURT RANDOLPH					
APVD 27OCT10 KURT RANDOLPH		NAME TAB, 4.75 [.187] PLAIN, MAG-MATE™ Slim Line —			
PRODUCT SPEC 108-1484					
APPLICATION SPEC 114-2140					
WEIGHT —					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE		CAGE CODE	
± —		A2		00779	
± —		DRAWING NO		C-1742860	
± 0.13 [.005]		RESTRICTED TO		—	
± —		SCALE		SHEET	
± —		10:1		1 OF 1	
± —		REV		1	
SEE TABLE		CUSTOMER DRAWING			