


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE SIZE AWG [mm ²]	COLOR	DIMENSIONS in. [mm]	
			L± .03 [0,8]	B± .01 [0,3]
ESV18BX	#22-18 [0,5-1,0]	RED	1.03 [26,2]	.17 [4,3]
ESV14BX	#16-14 [1,5-2,5]	BLUE	1.04 [26,4]	.20 [5,1]
ESV10BX	#12-10 [4,0-6,0]	YELLOW	1.18 [30,0]	.25 [6,4]

NOTES:

1. USED FOR:
- A. SOLID OR STRANDED COPPER WIRE
 - B. 221°F [105°C] MAX OPERATING TEMPERATURE
 - C. 600V MAX VOLTGE RATING
 - D. ESV10BX 300V MAX VOLTAGE RATING WITH 10 AWG SOLID WIRE
2. INSTALLATION TOOLS: CT-100A, CT-160, CT-260, CT-1550, CT-1551, CT-600A (CT-550CH), CT-2500 (CT-2550CH)
- A. #22-18 AWG [0,5-1,0 mm²]: CT-100A, CT-160, CT-260, CT-400, CT-600A (CT-550CH), CT-2500 (CT-2550CH)
 - B. #16-14 AWG [1,5-2,5 mm²]: CT-100A, CT-160, CT-260, CT-400, CT-460, CT-600-A, CT-2500
 - C. #12-10 [4,0-6,0 mm²] STRANDED AND #12 AWG SOLID COPPER WIRE WITH CT-1550 & CT-1551 TOOLS: CT-100A, CT-160, CT-260, CT-460, CT-600-A (CT-550CH), CT-2500 (CT-2550CH)
3. WIRE STRIP LENGTH: 5/16" ^{+1/32}₋₀ [7,9mm ^{+0,8}₋₀]
4. MATERIAL:
- A. STAMPING (#22-18 & #16-14): .03" [0,8] THK COPPER, TIN PLATED
 - B. STAMPING (#12-10): .04" [1,0] THK COPPER, TIN PLATED
 - C. HOUSING: VINYL
5. SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
6. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT
- | |
|--------|
| TITLE |
| STRONG |




LISTED
587H
E52164



CERTIFIED
LR31212

00	10.10.17	TMR	JHNU	RGB	DRAWING RELEASED	00123SH
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE					STRONGHOLD BUTT SPLICE, EXPANDED DIAMETER VINYL INSULATED, BUTTED SEAM #22-10 AWG	
					CUSTOMER DRAWING	
ITEM REVISION NAME			00123SHC/00			
DATASET FILE NAME			00123SHC_DC/00A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °					MATERIAL: SEE NOTES	
 THIRD ANGLE PROJECTION					DRAWING NUMBER: SH41181	
DRAWN BY		DATE	CHK	SCALE	SIZE	
TMR		10.10.17	JHNU	N.T.S.	SHT 1 OF 1	
					A	