






REV.	DESCRIPTION
A	Initial Release



PE Bag



Pin Assignments
Front View



UNIT:mm		
TOLERANCE		
$\pm 0.5\text{mm}$		

TITLE M12 D-Code Shielded Assy 4PIN F Conn. F Pin			
SCALE Free	SIZE A4	SHEET 1 OF 2	
REV. A	WC-REV. .0	QC: Inspection item	



Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO MSDS-04BFFC-SL7001	DRAWN BY Xiaofeng	DATE 2019/06/18
DWG NO MSDS-04BFFC-SL7001	CHECKED BY Li-Feng	DATE 2019/06/18
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2019/06/18

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	DESCRIPTION

M SDS - XX B F F C - S L 7 001



- Note:
- * IP: IP67.
 - * Housing: Thermoplastic, Black.
 - * Female Pin: Metal.
 - * Nut: Metal.
 - * O-Ring: Silicone, Grey.
 - * Clamp Ring: Metal.
 - * Sealing Nut: Metal..
 - * Seal: Silicone, Grey.
 - * Seal For Cable OD: $\varnothing 4.0\text{mm} \sim \varnothing 8.0\text{mm}$
 - * Applicable Wire gauge (Stranded wire cross section)
20AWG ~ 24AWG
 - * Mating Recommended tightening torque:
3~4 kgf.cm / 0.29~0.39 N.m
 - * Sealing-Nut Recommended tightening torque:
4~6 kgf.cm / 0.39~0.59 N.m
 - * Detailed applicable wire specifications may vary depending on the actual wire construction.

UNIT:mm				TITLE M12 D-Code Shielded Assy 4PIN F Conn. F Pin		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO MSDS-04BFFC-SL7001		DRAWN BY Xiaofeng		DATE 2019/06/18			
TOLERANCE ±0.5		SCALE 1:1						SIZE A4		SHEET 2 OF 2		DWG NO MSDS-04BFFC-SL7001		CHECKED BY Li-Feng	
		REV. A		WC-REV. .0				QC: Inspection item		CUSTOMER ALTW		APPROVED BY Jerry		DATE 2019/06/18	
1		2		3		4		5		6		7		8 W10814-03-2001A2	