





used for: D-SUB

NOTES:

1. METALSHELLS: STEEL; min. 320µ" TIN
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: 8µ" HARD GOLD OVER min. 50µ" NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. FRAME: STEEL; NICKEL PLATED
5. FLOAT MOUNTS: COPPER ALLOY; NICKEL PLATED
6. RIVETED INSERT: COPPER ALLOY; NICKEL PLATED
7. COLLAR: COPPER ALLOY; NICKEL PLATED
8. CONNECTOR IS PART MARKED: DSS1XPMAB01X CONEC ABC
9. = CHECK DIMENSION



Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY, WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance	dim. in mm
2006	date
drawn	10.04.
appd.	11.04.
norm	DIN 41652
d-old	

CONEC

scale:	2:1 (5:1)
material:	SEE NOTES
title:	
D-SUB MALE 9pos. SOLDER CUP with frame and float mount	
dwg no:	AutoCAD 2006
16K1A1798	
part no:	DSS1XPMAB01X

DIN-A
3
sh: 1/1