



LOC		DIST		REVISIONS				
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		B3		REV PER ECR-11-012858	16JUN2011	AY	SZ	
		B4		ADDED NEW DASH NUMBER -9	04SEP2012	CZ	SZ	
		B5		ADDED NEW DASH NUMBER 1-1	19APR2013	CZ	SZ	

- △1 "AMP", PART NUMBER AND DATE CODE TO BE MARKED IN AREA SHOWN
PARTS UNDER 2.00 LONG MAY BE MARKED ON BOTH SIDES
- △2 MATERIAL: HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC,UL94 V-0,BLACK.
SIGNAL CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
LP CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
- △3 CONTACT PLATING: NOBLE METAL PLATING ON CONTACT FUNCTIONAL AREA
OF POWER AND SIGNAL CONTACTS.
- △4 MECHANICAL CONNECTOR KEEP OUT ZONE
- △5 DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- △6 PCB - ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES
- △7 PCB - 0.0453 ±.0010 DRILLED HOLES PLATED WITH .0003 MIN Sn
OVER .001 TO .003 Cu PLATING TO ACHIEVE A .040 ±.030 HOLE
- △8 VARIABLE DIMENSIONS SHOW ON TABLE.
- △9 PLEASE REFER TO PART VIEW FOR DETAIL DIMENSIONS.
- △10 NOT RELEASED FOR PRODUCTION.



B5	.710	.115	-	-	.550	.1025	.900	4LP	1-6450863-1
	-	-	.250	.170	1.090	-	1.440	4P	6450863-9
	-	-	.200	.170	1.340	-	1.690	6HDP	6450863-8
	-	-	.200	.145	1.490	-	1.840	7HDP	6450863-6
	-	-	.300	.195	2.190	-	2.540	7ACP	6450863-5
△9	-	-	-	-	-	-	-	12 HDP	6450863-4
	2.700	-	△8	.145	2.540	-	2.890	12P	6450863-2
	D	T	S	K	U	R	L	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL

△6

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.01
1 PLC ±.01
2 PLC ±.01
3 PLC ±.005
4 PLC ±.0020
ANGLES ±.2°
FINISH

△7

DWN H.LIU 12JUN2008
CHK S.ZHAO 12JUN2008
APVD S.YAO

PRODUCT SPEC
108-2292
APPLICATION SPEC
114-13038

WEIGHT

CUSTOMER DRAWING

NAME

SIZE CAGE CODE DRAWING NO
A100779



RESTRICTED TO








SCALE N/A SHEET 1 OF 6 REV B5


TE Connectivity


VER RECEP ASSEMBLY
SHROT GUIDES, PRESS FIT
MULTI-BEAM XLE


©=6450863



PART NUMBER	ROWS		POWER							
			P7	P6	P5	P4	P3	P2	P1	
6450863-6	D C B A									
7HDP										


4805 (3/11)


PART NUMBER	ROWS		POWER				
			P4	P3	P2	P1	
6450863-9	D C B A						
4P							

4805 (3/11)

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
ES	00	-	-	SEE SHEET 1	-	-

B5

PART NUMBER		POWER				
		LP4	LP3	LP2	LP1	
I-6450863-1		LSI	LSI	LSI	LSI	
4 LP						



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.LIU 12JUN2008	 TE Connectivity		
		CHK S.ZHAO 12JUN2008			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S.YAO	NAME
		0 PLC ±.0005		PRODUCT SPEC	
		1 PLC ±.01		108-2292	
		2 PLC ±.005		APPLICATION SPEC	
		4 PLC ±.0020		114-13038	
ANGLES ±.0020		WEIGHT -		SIZE	CAGE CODE
FINISH		CUSTOMER DRAWING		DRAWING NO	
MATERIAL				A100779C=6450863	
				RESTRICTED TO	
				-	
				SCALE	
				N/A	
				SHEET	
				6	
				OF	
				REV	
				B5	