







2170753-2 AS SHOWN

- | | | | |
|-------|-------------|-------------|-------------|
| 23.0 | 1 | NETWORKING | 2170753-9 |
| 16.0 | 1 | SAN | 2170753-8 |
| 13.7 | 1 | PCI | 2170753-7 |
| 23.0 | 0 | NETWORKING | 2170753-6 |
| 16.0 | 0 | SAN | 2170753-5 |
| 13.7 | 0 | PCI | 2170753-4 |
| 23.0 | 2 | NETWORKING | 2170753-3 |
| 16.0 | 2 | SAN | 2170753-2 |
| 13.7 | 2 | PCI | 2170753-1 |
| DIM A | # REAR PINS | APPLICATION | PART NUMBER |


4805 (3/11)

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION			DATE	DWN	APVD
		- SEE SHEET 1			-	-	-


HEAT SINK OPTIONS



PCI HEAT SINK
SCALE 3:1




SAN HEAT SINK
SCALE 3:1




NETWORKING HEAT SINK
SCALE 3:1


OF REAR LEGS OPTIONS



2 REAR LEGS
SCALE 5:1







1 REAR LEG
SCALE 5:1



0 REAR LEG
SCALE 5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JASON YANG 01APR2014	 TE Connectivity		
		CHK SEAN HAN 30DEC2015			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.100 4 PLC ± ANGLES ± FINISH	NAME	CAGE ASSEMBLY, QSP28 1X1, THRU BEZEL, WITH EMI GASKET HEAT SINK	
MATERIAL - - -			PRODUCT SPEC 108-19428 APPLICATION SPEC 114-32023 WEIGHT -	SIZE	A100779C=2170753
				Customer Drawing	
				SCALE 4:1	SHEET 2 OF 5

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
-		SEE SHEET 1		-	-	-	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JASON YANG 01APR2014	 TE Connectivity	
		CHK SEAN HAN 30DEC2015		
DIMENSIONS:		APVD -	NAME	
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	CAGE ASSEMBLY, QSPF28 1X1, THRU BEZEL, WITH EMI GASKET HEAT SINK	
	0 P/LC ±0.25	108-19428	SIZE	
	1 P/LC ±0.25	APPLICATION SPEC	CAGE CODE	
	2 P/LC ±0.20	114-32023	DRAWING NO	
	3 P/LC ±0.100		RESTRICTED TO	
	4 P/LC ±0.100			
ANGLES		WEIGHT	A100779C=2170753	
MATERIAL	FINISH	Customer Drawing	SCALE 4:1	SHEET 3 OF 5
-	-			REV A
-	-			
-	-			





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-

D

C

B

A




C


B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JASON YANG 01APR2014	TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK SEAN HAN 30DEC2015		
DIMENSIONS:		APVD	NAME	
mm	0 PLC ± 0.25 1 PLC ± 0.25 2 PLC ± 0.20 3 PLC ± 0.100 4 PLC $\pm$ ANGLES $\pm$ FINISH	PRODUCT SPEC 108-19428 APPLICATION SPEC 114-32023 WEIGHT	CAGE CODE DRAWING NO. A100779C=2170753	RESTRICTED TO
MATERIAL		Customer Drawing	SCALE 4:1	SHEET 4 OF 5 REV A



RECOMMENDED PCB LAYOUT
BELLY TO BELLY TYPE OF 0 REAR HOLES OF LEGS
PCB TOLERANCE: ± 0.05
SCALE 6:1



DETAIL C
SCALE 8:1

4805 (3/11)