

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2011

ALL RIGHTS RESERVED.

VISTE SOLO PER RIFERIMENTO
VIEWS ONLY FOR REFERENCE

SEZ. A-A

COLOR CODE STRIP ALLOCATO IN QUESTA AREA DEL COPERCHIO
(COLOR CODE STRIP LOCATED ON THE COVER AS SHOWN)

SEZ. A-A

15.0 REF. +0 -0.3

24.5 -0.3

22.7

+0.1 -0.3

5.5 -0.3

2.5

1.5

+0.1 -0.3

1.0

9.2 -0.2

0.8 ±0.2

1.5 -0.3

0

23.6

14 MAX

30.4

9.0 ±0.2 (STOP ON COUNTERPART)

±0.2 ALTEZZA DELLA POLARIZZAZIONE (POLARIZATION HEIGHT)

3.0

4 "X"

2

1

4

5

ALETTE DI POLARIZZAZIONE A FILO BLOCCHETTO (VEDERE FOGLIO 2/2)
(POLARIZATION RIBS AT THE END OF CONNECTOR)
(SEE SHEET 2 OF 2)

QUOTA DI ARRESTO SULLA DIMA (STOP ON COUNTERPART)

DETAGLIO DEL CONTATTO, DIMENSIONI RIFERITE AL COMPONENTE INSERITO IN CAVITÀ
(ENLARGED VIEW OF TAB CONTACT DIM. REFERRED TO CONTACT INSERTED IN THE HOUSING CAVITY)

19.2 ±0.2

19.2 ±0.2

CONNETTORE COMPLETO DI CAVO (TERMINATED CONNECTOR)

24.5 MAX.

7

7.8

+0.1 -0.2

1.2 ±0.2

60°

DETAIL PN/s:
1-282006-3
2-282006-3
3-282006-3

POLARIZATION KEYS
(VIEW FROM "X")

5D 4D 3D 2S

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

18

DETAIL "B" FOR CAVITY 1 & 2

PN X-282002-8
PN I-2293382-2

0.3

5.2

+0.1 -0.2

4.1

0.5

1.4 ±0.2

6.5 ±0.2

2.5 REF.

0.75 REF.

0.75

2.45 REF.

5.0 PASSO (PITCH)

2.45 REF.

4

A

B

1

2

AMP

12

0.3

60°

-X-

-X-

NOTE/NOTES:

1 NUMERI DI IDENTIFICAZIONE CAVITÀ.
(CIRCUIT IDENTIFICATION)

2 MARCHIO DI FABBRICA LIBERA POSIZIONE).
(AMP LOGO FREE POSITION)

3 RETENTION TOOTH IS REQUESTED FOR THE 2 AND 3 POS. ONLY

4 PERTE PRELIMINARE, NON ANCORA IN PRODUZIONE
(PRELIMINARY PART, NOT YET RELEASED FOR PRODUCTION)

5 PER QUESTI P/N LA POLARIZZAZIONE POSTERIORE DEVE INTENDERSI COMPLETA, A FINE BLOCCHETTO.
(per la rappresentazione vedere foglio 1/2)
(FOR THE INDICATE P/N THE POLARIZATION MUST BE AT THE END OF CONNECTOR (see sheet 2 of 2).

6 CODIFICA CON DIFFERENTE DIMENSIONE.
(CODIFICATION WITH DIFFERENT DIMENSION).

7 BECOMES 6.5 FOR BOTH CAVITIES ON THE 2 POS., ON CAVITY N.1 AND N.3 ON THE 3 POS. AND ON CAVITY N.1 ON THE 4 POS. CONNECTOR

8 INCLUDE LA POLARIZZAZIONE DOVE E' ESISTENTE
(INCLUDING POLARIZATION KEY, WHEN EXISTING)

9 DETAIL FOR PN X-282002-8 AND PN I-2293382-2, SPECIAL VERSION, SEE ALSO NOTE 3

10 P/N NON RILASCIATO PER LA PRODUZIONE
(P/N NOT YET RELEASED FOR PRODUCTION)

11 ---

12 GEOMETRIA ALTERNATIVA DEL DENTINO DI AGGANCIAMENTO VEDI NOTA 3 PER ALTRI DETTAGLI
(ALTERNATIVE SHAPE FOR RETENTION TOOTH, SEE NOTE 3 FOR ADDITIONAL DETAILS)

13 STATO DI FORNITURA: CONFEZIONAMENTO IN "VASSOI + SCATOLA"
(PACKAGING: "ON TRAY PLUS CARTON BOX")

14 CONFEZIONAMENTO IN BOBINA OBSOLETO
(PACKAGING: ON REEL OBSOLETE)

15 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

16 THE DESIRED POLARIZATION CAN BE OBTAINED BY THE TERMINATION MACHINE

17 EXCEPTION MADE FOR PN FOR THIS PN CAVITY 1 IS WITHOUT RETENTION TOOTH AND HAS THE SAME DESIGN AS THE CAVITY N.2

18 OBSOLETE PART

DETAIL FOR PN 0-282233-2 ONLY

4.2

10.8 REF.

1.4

6

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

0.3

±

SEE TABLE

SEE TABLE

DWN G. ENDRIZZI 23JUL1995

CHK G. TURCO 23JUL1995

APVD G. TURCO 23JUL1995

PRODUCT SPEC

108-20065-1, 108-20065-2

APPLICATION SPEC

114-20016, 114-20016-1

WEIGHT

-

Customer Drawing

SCALE

-

SHEET 1 OF 7

REV. ABI

TE Connectivity

MONO-SHAPE MK1
TAB CONNECTORS 2-10 POS.

SIZE

A2

CAGE CODE

07779

DRAWING NO

C-282002

RESTRICTED TO

-

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

AB

ECR-21-106443

07JUL2021

SM

FL

ABI

ECR-21-110402

30AUG2021

KD

FL

1471-9 (3/11)

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2011

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
-	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
SEE SHEET 1							

VISTE SOLO PER RIFERIMENTO

VIEWS ONLY FOR REFERENCE

TE PART NUMBER ASSY CONN.

NUMERO DI VIE	CONFIGURAZIONE (Vista connettore dall'alto)①	VERSIONE PEZZI IN VASSOIO		VERSIONE PEZZI SCIOLTI		POSIZIONE POLARIZ. (LATO POSTERIORE)	POSIZIONE AGGANCIO (LATO ANTERIORE)	POSIZIONE CODIFICA SPECIALE (LATO ANTERIORE)	L+0.2 L-0.3 (mm) 8	NOTE MARCHIATURA CON BANDA COLORATA	
NO OF POS	CONFIGURATION (View from top side) ①	TRAY PACKAGING VERSION	PART REV	LOOSE PIECES PACKAGING VERSION	PART REV	POLARIZ. POSITION (BACK SIDE)	LOCKING POSITION (FRONT SIDE)	SPECIAL COD. POSITION (FRONT SIDE)	L+0.2 L-0.3 (mm)	NOTE STRIP COLOUR	POSSIBLE RAST 5 POLARIZ. 16
2		4-282002-1	AA	-	-	2S 5	1-2	-	9.9	NERO BLACK	02-C 7
2		1-282002-1	V	2-282002-1	V	2S 5	1-2	-	9.9	NERO BLACK	02-C
2		1-282002-2	V	2-282002-2	V	1S 2D	1-2	-	9.9	GRIGIO GREY	02-B 02-E 02-F
2		1-282002-3	V	2-282002-3	V	2D	1-2	-	9.9	ROSSO RED	02-L
2		1-282002-4	V	2-282002-4	V	1D 5 2S 5	1-2	-	9.9	BLU BLUE	02-A
2		1-282002-5	V	2-282002-5	V	1D	1-2	-	9.9	NERO BLACK	02-Q
2		3-282002-5	AA	-	-	1D	1-2	-	9.9	NERO BLACK	02-Q 7
2		1-282002-6	V	2-282002-6	V	-	1-2	-	9.9	NERO BLACK	-
2		1-282002-7	V	2-282002-7	V	-	1-2	-	9.9	-	-
2		1-282002-8	V	2-282002-8	V	1S 2D	1-2	-	9.9	VERDE GREEN	02-B 02-E 02-F 7
2		2-282002-9	I	-	-	1D 2D	1-2	-	9.9	-	-
2		3-282002-0	I	-	-	1S 1D	1-2	-	9.9	-	-
2		3-282002-4	AA	-	-	1D 5 2S 5	1-2	-	9.9	-	02-A 7
2		5-282002-2	A	-	-	1S 2D	1-2	-	9.9	YELLOW	02-B 02-E 02-F
2		6-282002-0	AA	-	-	1S 5 2S 5	1-2	-	9.9	RED	- 7

LEGENDA

(DESCRIPTION)

① AMP MONO-SHAPE, TAB CONNECTORS
(ESEMPIO DI CONFIGURAZIONE)
(EXAMPLE OF CONFIGURATION)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

0.3

FINISH

SEE TABLE

DWN G. ENDRIZZI 23JUL1995
CHK G. TURCO 23JUL1995
APVD G. TURCO 23JUL1995
PRODUCT SPEC
108-20065-1, 108-20065-2
APPLICATION SPEC
114-20016, 114-20016-1
WEIGHT -
Customer Drawing

TE Connectivity

MONO-SHAPE MK1
TAB CONNECTORS 2-10 POS.

SIZE
A200779

CAGE CODE
C-282002

DRAWING NO
-

RESTRICTED TO
-

SCALE -

SHEET 2 OF 7

REV. A

1471-9 (3/11)

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2011

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

VISTE SOLO PER RIFERIMENTO

VIEWS ONLY FOR REFERENCE

LEGENDA

(DESCRIPTION)

AMP MONO-SHAPE, TAB CONNECTORS

(ESEMPIO DI CONFIGURAZIONE)

(EXAMPLE OF CONFIGURATION)

1

2

3

4

5

6

7

8

LATO BANDA COLORATA

(COLOR STRIP SIDE)

AGGANCI O

(LOCKING LANCE)

CODIFICA

(CODIFICATION)

POLARIZZAZIONE

(POLARIZATION)

POLARIZZAZIONE

(POLARIZATION)

AGGANCI O

(LOCKING LANCE)

CODIFICA

(CODIFICATION)

CODIFICA SPECIALE

(SPECIAL CODIFICATION)

TE PART NUMBER ASSY CONN.		VERSIONE PEZZI IN VASSOIO		VERSIONE PEZZI SCIOLTI		POSIZIONE POLARIZ. (LATO POSTERIORE)	POSIZIONE AGGANCI O (LATO ANTERIORE)	POSIZIONE CODIFICA SPECIALE (LATO ANTERIORE)	L+0.2 L-0.3 (mm) 8	NOTE MARCHIATURA CON BANDA COLORATA	
NUMERO DI VIE	CONFIGURAZIONE (Vista connettore dall'alto)①	TRAY PACKAGING VERSION	PART REV	LOOSE PIECES PACKAGING VERSION	PART REV	POLARIZ. POSITION (BACK SIDE)	LOCKING POSITION (FRONT SIDE)	SPECIAL COD. POSITION (FRONT SIDE)	L+0.2 L-0.3 (mm)	NOTE STRIP COLOUR	POSSIBLE RAST 5 POLARIZ. 16
3		1-282003-1	V	2-282003-1	V	1D	1-2	-	14.9	ARANCIO ORANGE	03-A 03-I
3		4-282003-1	AA	-	-	1D 5	1-2	-	14.9	ARANCIO ORANGE	03-A 03-I 7
3		1-282003-2	V	2-282003-2	V	2D 3D	2-3	-	14.9	BLU BLUE	03-B
3		1-282003-3	V	2-282003-3	V	1S 3D	1-2	-	14.9	VERDE GREEN	03-F
3		1-282003-4	V	2-282003-4	V	2D 3D	2-3	-	14.9	ROSSO RED	03-B
3		1-282003-5	V	2-282003-5	V	2D 3D	2-3	-	14.9	GRIGIO GREY	03-B
3		1-282003-6	V	2-282003-6	V	-	1-2	-	14.9	VIOLA VIOLET	-
3		1-282003-7	V	-	-	2D 3D	2-3	-	14.9	NERO BLACK	03-B
3		3-282003-3	I	-	-	1S 1D	1-2	-	14.9	-	-
3		3-282003-4	I	-	-	1D - 2S 2D - 3S	1-2	-	14.9	-	-
3		3-282003-5	I	-	-	1S 3D	2-3	-	14.9	-	-
3		3-282003-6	AA	-	-	1S - 1D 2S - 2D	1-2	-	14.9	-	-
3		3-282003-7	I	-	-	1S	1-2	-	14.9	-	-
3		0-282233-2	V	2-282233-2	V	1S 5	1-2	-	14.9	-	03-D 8
3		1-284396-1	Z	-	-	2S	2-3	-	14.9	NERO BLACK	-

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

MATERIAL

SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

0.3

FINISH

SEE TABLE

DWN G. ENDRIZZI 23JUL1995
CHK G. TURCO 23JUL1995
APVD G. TURCO 23JUL1995
PRODUCT SPEC
108-20065-1, 108-20065-2
APPLICATION SPEC
114-20016, 114-20016-1
WEIGHT -
Customer Drawing

NAME

MONO-SHAPE MK1
TAB CONNECTORS 2-10 POS.

SIZE
A200779

CAGE CODE
C-282002

DRAWING NO

RESTRICTED TO

SCALE -

SHEET 3 OF 7

REV. A

TE Connectivity

AB

1471-9 (3/11)

1

2

3

4

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

NUMERO DI VIE	CONFIGURAZIONE (Vista connettore dall'alto) ①	TE PART NUMBER ASSY CONN.		VERSIONE PEZZI IN VASSOIO	VERSIONE PEZZI SCIOLTI	POSIZIONE POLARIZ. (LATO POSTERIORE)	POSIZIONE AGGANCIO (LATO ANTERIORE)	POSIZIONE CODIFICA SPECIALE (LATO ANTERIORE)	L+0.2 L-0.3 (mm) ⑧	NOTE MARCHIATURA CON BANDA COLORATA	
NO OF POS	CONFIGURATION (View from top side) ①	TRAY PACKAGING VERSION	PART REV	LOOSE PIECES PACKAGING VERSION	PART REV	POLARIZ. POSITION (BACK SIDE)	LOCKING POSITION (FRONT SIDE)	SPECIAL COD. POSITION (FRONT SIDE)	L+0.2 L-0.3 (mm)	NOTE STRIP COLOUR	POSSIBLE RAST 5 POLARIZ. ⑩
4		1-282004-1	V	2-282004-1	V	1D ⑤	1-2 3-4	2D	19.9	GRIGIO GREY	04-A
4		1-282004-2	V	2-282004-2	V	3D ⑤	2-3	-	19.9	NERO BLACK	04-D
4		1-282004-3	V	2-282004-3	V	1D ⑤	1-2 3-4	2D	19.9	ROSSO RED	04-A
4		1-282004-4	S	-	-	3D	1-2	-	19.9	BLU BLUE	-
4		3-282004-4	AA	-	-	4D 1S	3-4 1-2	-	19.9	-	04-A
4		4-282004-4	I	-	-	4D 1S-1D-2S-2D 3S-3D-4S-4D AS-BD-CS-DD	3-4 1-2	-	19.9	-	-
5		1-282005-1	V	2-282005-1	V	4D ⑤	4-5	-	24.9	ROSSO RED	-
5		1-284545-1	Z	-	-	2S ⑤	4-5	-	24.9	ROSSO RED	-
5		1-284545-2	A	-	-	1S 5D	- 3-4	3D	24.9	-	-
5		1-284545-3	A	-	-	1S 5D	1-2 3-4	-	24.9	BLU BLUE	-
5		1-293003-5	Z	-	-	-	4-5	-	24.9	NERO BLACK	-
6		1-282006-2	V	2-282006-2	V	2S 5D	2-3	-	29.9	VIOLA VIOLET	-
6		1-282006-3	V	2-282006-3	V	2S - 3D 4D - 5D	4-5	-	29.9	-	-
6		2-282006-4	V	-	-	3D 5D	-	5S	29.9	NERO BLACK	-
6		1-284745-1	Z	-	-	6D ⑤	4-5	-	29.9	ROSSO RED	-
6		1-284745-2	I	-	-	6D ⑤	-	4D	29.9	RED	-
6		1-284745-3	AA	-	-	5D ⑤	3-4	-	29.9	VIOLET	-
6		1-284745-4	AA	-	-	1S ⑤	2-3	-	29.9	ORANGE	-
7		1-282007-1	V	2-282007-1	V	1D ⑤ 5D	1-2 5-6	3S	34.9	-	-
7		2-282007-2	V	-	-	4D 6D	-	6S	34.9	VIOLA VIOLET	-
7		2-282007-3	I	-	-	1S - 2S - 2D 3S - 3D - 4D 5S - 6S - 6D 7S - 7D	1-2 5-6	-	34.9	-	-
7		3-282007-2	AA	-	-	-	1-2	5S	34.9	-	-
7		1-284397-1	Z	-	-	2D	1-2 5-6	-	34.9	NERO BLACK	-
7		1-293004-7	Z	-	-	-	1-2	-	34.9	ROSSO RED	-
7		2-293004-7	I	-	-	-	1-2	-	34.9	GRIGIO GREY	-
8		0-284085-1	V	2-284085-1	V	2D - 6S 4D - 6D	-	4S	39.9	-	-
8		0-284085-2	V	2-284085-2	V	-	2-3	-	39.9	VIOLA VIOLET	-

VISTE SOLO PER RIFERIMENTO
VIEWS ONLY FOR REFERENCE

LEGENDA
(DESCRIPTION)

① AMP MONO-SHAPE, TAB CONNECTORS
(ESEMPIO DI CONFIGURAZIONE)
(EXAMPLE OF CONFIGURATION)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES

±:
±:
±:
±:
±:
±

>0.3

±

FINISH

SEE TABLE

DWN
G. ENDRIZZI
CHK
G. TURCO
APVD
G. TURCO
PRODUCT SPEC
APPLICATION SPEC
114-20016, 114-20016-1
WEIGHT
--

23JUL1995
23JUL1995
23JUL1995

Customer Drawing

TE Connectivity

MONO-SHAPE MK1
TAB CONNECTORS 2-10 POS.

SIZE
A260779

CAGE CODE
C-282002

DRAWING NO

RESTRICTED TO
-
REV
ABI

SCALE
-

SHEET
4


OF
7

1471-9 (3/11)

NUMERO DI VIE	CONFIGURAZIONE (Vista connettore dall'alto) ①	TE PART NUMBER ASSY CONN.				POSIZIONE POLARIZ. (LATO POSTERIORE)	POSIZIONE AGGANCIO (LATO ANTERIORE)	POSIZIONE CODIFICA SPECIALE (LATO ANTERIORE)	L +0.2 L -0.3 (mm) ⑧	NOTE MARCHIATURA CON BANDA COLORATA	
		VERSIONE PEZZI IN VASSOIO	VERSIONE PEZZI SCIOLTI								
NO OF POS	CONFIGURATION (View from top side) ①	TRAY PACKAGING VERSION	PART REV	LOOSE PIECES PACKAGING VERSION	PART REV	POLARIZ. POSITION (BACK SIDE)	LOCKING POSITION (FRONT SIDE)	SPECIAL COD. POSITION (FRONT SIDE)	L +0.2 L -0.3 (mm)	NOTE STRIP COLOUR	POSSIBLE RAST 5 POLARIZ. ⑩
10		1-282010-1	V	2-282010-1	V	6D 8S	4-5 8-9	6S	49.9	-	-
10		0-284004-1	V	-	-	6D 8S	4-5 8-9	6S	49.9	-	-

VISTE SOLO PER RIFERIMENTO
VIEWS ONLY FOR REFERENCE

LEGENDA
(DESCRIPTION)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. ENDRIZZI 23JUL1995	 TE Connectivity			
DIMENSIONS: mm		CHK G. TURCO 23JUL1995				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH	APVD G. TURCO 23JUL1995	NAME MONO-SHAPE MK1 TAB CONNECTORS 2-10 POS. -			
		PRODUCT SPEC 108-20065-1, 108-20065-2				
MATERIAL	SEE TABLE	APPLICATION SPEC 114-20016, 114-20016-1	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT --	A200779		C=282002	-
Customer Drawing		SCALE -	SHEET 5	OF 7	REV A1	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2011

ALL RIGHTS RESERVED.

LOC-

DIST-

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

1

2

3

4

PA GF, UL-V0 GWEPT 750° C NO FLAME, NATURAL

		ON TRAY		LOOSE PIECES		SEE SHEET 1 FOR ADDITIONAL DETAILS AND NOTES						
No. of POS.	CONFIGURATION ONLY FOR REF	P/N ASS'Y	PART REV.	P/N ASS'Y	PART REV.	POLARIZ. POSITION (BACK SIDE)	LOCKING POSITION (FRONT SIDE)	SPECIAL CODIFICAT. POSITION (FRONT SIDE)	L (mm)	COLOR CODE	POSSIBLE RAST 5 POLARIZ.	
4		4-2293382-4	AA			1D	1-2 3-4	-	19.9			
4		5-2293382-4	AB			3D	2-3	-	19.9	BLACK	04-D	
5		2293382-5	AA			-	4-5	-	24.9			
5		1-2293382-5	AA			-	3-4	3S	24.9			
5		2-2293382-5	AA			1S 2D 4D 5D	1-2 4-5	-	24.9			
	6	2293382-6	I			TBD	TBD	TBD	29.9			
	7	2293382-7	I			-	1-2 5-6	-	34.9			
	7	2-2293382-7	I			1S 2S 2D 3S 3D 4D 5S 6S 6D 7S 7D	1-2 5-6		34.9			
	8	2293382-8	I			TBD	TBD	TBD	39.9			
	9	2293382-9	I			TBD	TBD	TBD	44.9			
	10	1-2293382-0	I			6D 8S	4-5 8-9	6S	49.9			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

SEE TABLE

DWN G. ENDRIZZI 23JUL1995
CHK G. TURCO 23JUL1995
APVD G. TURCO 23JUL1995
PRODUCT SPEC 108-20065-1, 108-20065-2
APPLICATION SPEC 114-20016, 114-20016-1
WEIGHT -

Customer Drawing

TE Connectivity

MONO-SHAPE MK I
TAB CONNECTORS 2-10 POS.
-

SIZE A2
CAGE CODE b0779
DRAWING NO C-282002
RESTRICTED TO -

SCALE -
SHEET 7 OF 7
REV. A

1471-9 (3/11)

A

B

C

D