

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	P	CUTTING BURR DETAILS ADDED	20NOV2018	RK	PS


1. MATERIAL:
HOUSING: POLYAMIDE 6, UL94V-2.
COLOR: NATURAL (OFF WHITE)
TUBULAR CONTACT: BRASS TIN, PLATED.
SCREWS: M3, STEEL, ZINC PLATED W/ NON-
HEXAVALENT CHROMATE (CHROME III).
WIRE PROTECTOR: STAINLESS STEEL.

2. ELECTRICAL:
CURRENT RATING: 30A.
OPERATING VOLTAGE: 250V.
WIRE RANGE: 16-26 AWG.

3. CONTINUOUS OPERATING TEMP.: 100°C MAX.


4 CUTTING PROJECTION CAN BE ON BOTH SIDES
DEPENDING ON CUTTING LOCATION.

5. CUTTING BURR MAX. 1mm ALLOWED.



1776322-4 AS SHOWN

80.0	94.0	12	TSB23012DSDM	1-1776322-2
72.0	86.0	11	TSB23011DSDM	1-1776322-1
64.0	78.0	10	TSB23010DSDM	1-1776322-0
56.0	70.0	9	TSB23009DSDM	1776322-9
48.0	62.0	8	TSB23008DSDM	1776322-8
40.0	54.0	7	TSB23007DSDM	1776322-7
32.0	46.0	6	TSB23006DSDM	1776322-6
24.0	38.0	5	TSB23005DSDM	1776322-5
16.0	30.0	4	TSB23004DSDM	1776322-4
8.0	22.0	3	TSB23003DSDM	1776322-3
—	14.0	2	TSB23002DSDM	1776322-2
—	6.0	1	TSB23001DSDM	1776322-1
DIM B	DIM A	NO. OF POS.	CATALOG NUMBER	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL	3/21/05	TE Connectivity Ltd.				
		CHK C RICHARD	3/21/05					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C RICHARD	3/21/05	NAME 8mm PITCH, TERMINAL BLOCK – HIGH CURRENT W/ WIRE PROTECTOR —				
	0 PLC ± – 1 PLC ± 0.3 2 PLC ± 0.25 3 PLC ± – 4 PLC ± – ANGLES ± 2°	PRODUCT SPEC —						
MATERIAL SEE NOTES	FINISH SEE NOTES	APPLICATION SPEC —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		WEIGHT —	A3	00779	C=1776322	—		
CUSTOMER DRAWING						SCALE NTS	SHEET 1 OF 1	REV P