




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B6	REVISED PER ECN-23-242776	14DEC2023	WLS	VS




	0.15
---	------

INCLUDES CONTACT TAILS,
HOUSING STANDOFFS,
AND BOARDLOCKS.



- 1 MATERIAL: HOUSING - UL 94V-O RATED HIGH TEMP NYLON, COLOR BLACK.
CONTACTS - BRASS
HOLDDOWNS - PHOSPHOR BRONZE.
- 2 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 3 PLATING: CONTACTS - 0.38 μ m MINIMUM GOLD ON MATING END,
2.54 μ m MINIMUM MATTE TIN ON SOLDER TAILS,
ALL OVER 1.27 μ m MINIMUM NICKEL.
HOLDDOWNS - 2.54 μ m MINIMUM MATTE TIN OVER 1.27 μ m MINIMUM NICKEL.
- 4 COUNTERPART RECOMMENDED IS PN 1445022 OR 2008571 (DASH ACC. TO NUMBER OF POSITION).
- 5 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.



	33.00	40.27	40.00	12	3-1445091-2
OBSOLETE	30.00	37.27	37.00	11	3-1445091-1
OBSOLETE	27.00	34.27	34.00	10	3-1445091-0
	24.00	31.27	31.00	9	2-1445091-9
OBSOLETE	21.00	28.27	28.00	8	2-1445091-8
	18.00	25.27	25.00	7	2-1445091-7
	15.00	22.27	22.00	6	2-1445091-6
	12.00	19.27	19.00	5	2-1445091-5
	9.00	16.27	16.00	4	2-1445091-4
	6.00	13.27	13.00	3	2-1445091-3
	3.00	10.27	10.00	2	2-1445091-2
	DIM Z	DIM V	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 090CT2000 J. ROOT CHK 17-APR-2001 K. WHITAKER APVD 17-APR-2001 C. JONES		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±° MATERIAL FINISH		NAME RIGHT ANGLE SURF MOUNT HEADER ASSY, 0.38 MIC GOLD CONTACTS, W/SURF MNT. HOLDDONWS, SGL ROW, MICRO MATE-N-LOK™	
		PRODUCT SPEC 108-1836 APPLICATION SPEC 114-13000		SIZE A2	
		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-1445091	
				RESTRICTED TO -	
				SCALE 4:1 SHEET 1 OF 2 REV B6	

